

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223234

Luminaire Tested: **LD2B10D010 EU2B10NFL258040 2LBDLC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223234  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10NFL258040 2LBDLC\*MMS  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
NARROW FLOOD OPTIC  
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1002.0 lumens  
Efficiency: N/A  
Efficacy: 97.3 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223234

CATALOG NUMBER: LD2B10D010 EU2B10NFL258040 2LBDLC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P223234

CATALOG NUMBER: LD2B10D010 EU2B10NFL258040 2LBDLC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 115 | 113 | 112 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 102 | 100 | 100 | 99  | 97  | 97  | 97  | 97  |
| 2   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 104 | 102 | 100 | 101 | 99  | 98  | 98  | 97  | 96  | 95  | 95  | 95  | 95  |
| 3   | 109 | 105 | 101 | 99  | 107 | 103 | 100 | 98  | 101 | 98  | 96  | 99  | 97  | 95  | 96  | 95  | 93  | 92  | 92  | 92  | 92  |
| 4   | 106 | 101 | 97  | 95  | 104 | 100 | 97  | 94  | 98  | 95  | 93  | 96  | 94  | 92  | 95  | 93  | 91  | 90  | 90  | 90  | 90  |
| 5   | 103 | 98  | 94  | 91  | 102 | 97  | 94  | 91  | 95  | 92  | 90  | 94  | 91  | 89  | 93  | 90  | 89  | 88  | 88  | 88  | 88  |
| 6   | 101 | 95  | 91  | 89  | 99  | 94  | 91  | 88  | 93  | 90  | 88  | 92  | 89  | 87  | 91  | 88  | 87  | 86  | 86  | 86  | 86  |
| 7   | 98  | 92  | 89  | 86  | 97  | 92  | 88  | 86  | 91  | 88  | 85  | 90  | 87  | 85  | 89  | 86  | 85  | 84  | 84  | 84  | 84  |
| 8   | 96  | 90  | 86  | 84  | 95  | 90  | 86  | 84  | 89  | 86  | 83  | 88  | 85  | 83  | 87  | 85  | 83  | 82  | 82  | 82  | 82  |
| 9   | 94  | 88  | 84  | 82  | 93  | 88  | 84  | 82  | 87  | 84  | 82  | 86  | 83  | 81  | 85  | 83  | 81  | 80  | 80  | 80  | 80  |
| 10  | 92  | 86  | 82  | 80  | 91  | 86  | 82  | 80  | 85  | 82  | 80  | 84  | 82  | 80  | 84  | 81  | 79  | 79  | 79  | 79  | 79  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2302578 |
| 5°  | 2126021 |
| 10° | 1439045 |
| 15° | 489593  |
| 20° | 179804  |
| 25° | 95350   |
| 30° | 49021   |
| 35° | 22887   |
| 40° | 7484    |
| 45° | 3780    |
| 50° | 1808    |
| 55° | 675     |
| 60° | 775     |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P223234

CATALOG NUMBER: LD2B10D010 EU2B10NFL258040 2LBDLC\*MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 465.1  | 46.4      |
| 10°-20°   | 391.1  | 39.0      |
| 20°-30°   | 107.3  | 10.7      |
| 30°-40°   | 31.3   | 3.1       |
| 40°-50°   | 5.8    | 0.6       |
| 50°-60°   | 1.3    | 0.1       |
| 60°-70°   | 0.1    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 963.5  | 96.2      |
| 0°-40°    | 994.8  | 99.3      |
| 0°-60°    | 1001.9 | 100.0     |
| 0°-90°    | 1002.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1002.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5944 |      |
| 5°  | 5468 | 465  |
| 15° | 1221 | 391  |
| 25° | 223  | 107  |
| 35° | 48   | 31   |
| 45° | 7    | 6    |
| 55° | 1    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P223234

CATALOG NUMBER: LD2B10D010 EU2B10NFL258040 2LBDLC\*MMS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 5944.5 |
| 1°    | 5909.9 |
| 2°    | 5848.8 |
| 3°    | 5760.9 |
| 4°    | 5640.5 |
| 5°    | 5467.8 |
| 6°    | 5231.9 |
| 7°    | 4936.8 |
| 8°    | 4576.6 |
| 9°    | 4151.2 |
| 10°   | 3658.7 |
| 11°   | 3118.8 |
| 12°   | 2557.2 |
| 13°   | 2021.3 |
| 14°   | 1564.3 |
| 15°   | 1220.9 |
| 17.5° | 688.9  |
| 20°   | 436.2  |
| 22.5° | 310.9  |
| 25°   | 223.1  |
| 27.5° | 157.9  |
| 30°   | 109.6  |
| 32.5° | 77.0   |
| 35°   | 48.4   |
| 37.5° | 19.7   |
| 40°   | 14.8   |
| 42.5° | 10.9   |
| 45°   | 6.9    |
| 47.5° | 3.9    |
| 50°   | 3.0    |
| 52.5° | 2.0    |
| 55°   | 1.0    |
| 57.5° | 1.0    |
| 60°   | 1.0    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P223234

CATALOG NUMBER: LD2B10D010 EU2B10NFL258040 2LBDLC\*MMS

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |  |     |
|-------|--|-----|
| 85°   |  | 0.0 |
| 87.5° |  | 0.0 |



(END OF REPORT)