

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224915

Luminaire Tested: **LD2B10D010 EU2B10FL409040 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10FL409040 2LBD*H
Description: 1000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 873.9 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224915

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224915

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	94	96	94	93	91				91
3	106	100	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87				87
4	102	96	91	88	100	94	90	87	92	89	86	91	88	85	89	86	84	83				83
5	98	91	86	83	96	90	86	82	89	85	82	87	84	81	86	83	80	79				79
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76				76
7	91	83	78	75	90	83	78	75	82	77	74	80	77	74	79	76	74	73				73
8	88	80	75	72	87	79	75	72	78	74	71	77	74	71	77	73	71	70				70
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67				67
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64				64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	810560
5°	793593
10°	698932
15°	548381
20°	364142
25°	209036
30°	104840
35°	48421
40°	19670
45°	8819
50°	4580
55°	2836
60°	1317
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224915

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	21.3
10°-20°	370.1	42.4
20°-30°	230.0	26.3
30°-40°	69.4	7.9
40°-50°	14.2	1.6
50°-60°	3.6	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	786.5	90.0
0°-40°	855.9	97.9
0°-60°	873.7	100.0
0°-90°	873.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	873.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2093	
5°	2041	186
15°	1368	370
25°	489	230
35°	102	69
45°	16	14
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224915

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2092.6
1°	2085.9
2°	2076.6
3°	2069.8
4°	2059.6
5°	2041.0
6°	2011.4
7°	1970.8
8°	1912.4
9°	1846.4
10°	1777.0
11°	1703.4
12°	1626.4
13°	1546.0
14°	1458.0
15°	1367.5
17.5°	1124.6
20°	883.4
22.5°	670.2
25°	489.1
27.5°	345.2
30°	234.4
32.5°	154.0
35°	102.4
37.5°	63.5
40°	38.9
42.5°	25.4
45°	16.1
47.5°	10.2
50°	7.6
52.5°	5.1
55°	4.2
57.5°	2.5
60°	1.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224915

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)