

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264185

Luminaire Tested: **LD2B10D010 EU2B1010SP159024 2LBD*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP159024 2LBD*LI
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 691.0 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264185

CATALOG NUMBER: LD2B10D010 EU2B1010SP159024 2LBD*LI

Luminous Intensity Polar Plot





TEST NUMBER: P264185

CATALOG NUMBER: LD2B10D010 EU2B1010SP159024 2LBD*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	97	96	95	94	93	92													
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	95	94	93	92	91	90													
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94	93	92	91	90	89	88													
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92	91	90	89	88	87	86													
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90	89	88	87	86	85	84													
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89	88	87	86	85	84	83													
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87	86	85	84	83	82	81													
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86	85	84	83	82	81	80													
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	84	83	82	81	80	79	78													
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83	82	81	80	79	78	77													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3260579
5°	2613514
10°	1140665
15°	353501
20°	123223
25°	54436
30°	24667
35°	12829
40°	7278
45°	3489
50°	2149
55°	1204
60°	691
65°	817
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264185

CATALOG NUMBER: LD2B10D010 EU2B1010SP159024 2LBD*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	400.7	58.0
10°-20°	219.5	31.8
20°-30°	50.0	7.2
30°-40°	14.4	2.1
40°-50°	4.4	0.6
50°-60°	1.3	0.2
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	670.2	97.0
0°-40°	684.6	99.1
0°-60°	690.4	99.9
0°-90°	691.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	691.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6609	
5°	5277	401
15°	692	219
25°	100	50
35°	21	14
45°	5	4
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264185

CATALOG NUMBER: LD2B10D010 EU2B1010SP159024 2LBD*LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6608.9
1°	6526.6
2°	6355.7
3°	6090.5
4°	5726.0
5°	5277.2
6°	4726.9
7°	4112.1
8°	3470.4
9°	2849.2
10°	2276.9
11°	1792.6
12°	1411.1
13°	1110.5
14°	877.2
15°	692.1
16°	546.0
17°	434.7
18°	349.6
19°	284.4
20°	234.7
22.5°	151.7
25°	100.0
26°	84.4
27°	71.6
28°	60.3
29°	50.3
30°	43.3
32.5°	29.8
35°	21.3
37.5°	15.6
40°	11.3
42.5°	7.8
45°	5.0
47.5°	3.5
50°	2.8
52.5°	2.1
55°	1.4
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.7



TEST NUMBER: P264185

CATALOG NUMBER: LD2B10D010 EU2B1010SP159024 2LBD*LI

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)