

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222551

Luminaire Tested: **LD2B10D010 EU2B10NFL259040 2LBDL\*H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P222551  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10NFL259040 2LBDL\*H  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
NARROW FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 817.9 lumens  
Efficiency: N/A  
Efficacy: 79.4 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P222551

CATALOG NUMBER: LD2B10D010 EU2B10NFL259040 2LBDL\*H

### Luminous Intensity Polar Plot





TEST NUMBER: P222551

CATALOG NUMBER: LD2B10D010 EU2B10NFL259040 2LBDL\*H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	87	85	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1879519
5°	1735406
10°	1174654
15°	399647
20°	146786
25°	77828
30°	39986
35°	18678
40°	6118
45°	3068
50°	1446
55°	540
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222551

CATALOG NUMBER: LD2B10D010 EU2B10NFL259040 2LBDL\*H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	379.7	46.4
10°-20°	319.2	39.0
20°-30°	87.6	10.7
30°-40°	25.5	3.1
40°-50°	4.7	0.6
50°-60°	1.1	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	786.5	96.2
0°-40°	812.0	99.3
0°-60°	817.8	100.0
0°-90°	817.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	817.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4852	
5°	4463	380
15°	997	319
25°	182	88
35°	40	26
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222551

CATALOG NUMBER: LD2B10D010 EU2B10NFL259040 2LBDL\*H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4852.3
1°	4824.1
2°	4774.1
3°	4702.4
4°	4604.2
5°	4463.2
6°	4270.6
7°	4029.7
8°	3735.7
9°	3388.5
10°	2986.5
11°	2545.8
12°	2087.4
13°	1649.9
14°	1276.9
15°	996.6
17.5°	562.3
20°	356.1
22.5°	253.8
25°	182.1
27.5°	128.9
30°	89.4
32.5°	62.8
35°	39.5
37.5°	16.1
40°	12.1
42.5°	8.9
45°	5.6
47.5°	3.2
50°	2.4
52.5°	1.6
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222551

CATALOG NUMBER: LD2B10D010 EU2B10NFL259040 2LBDL\*H

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)