

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224721

Luminaire Tested: **LD2B10D010 EU2B10FL409024 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224721
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10FL409024 2LBD*
MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 732.5 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224721

CATALOG NUMBER: LD2B10D010 EU2B10FL409024 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224721

CATALOG NUMBER: LD2B10D010 EU2B10FL409024 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95				
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91				91				
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86				86				
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82				82				
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79				79				
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75				75				
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72				72				
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69				69				
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66				66				
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64				64				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	663136
5°	651050
10°	578772
15°	455187
20°	302888
25°	173905
30°	87844
35°	41328
40°	16636
45°	8217
50°	4520
55°	3174
60°	2944
65°	1741
70°	2152
75°	1347
80°	2008
85°	0



TEST NUMBER: P224721

CATALOG NUMBER: LD2B10D010 EU2B10FL409024 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	20.9
10°-20°	307.5	42.0
20°-30°	191.3	26.1
30°-40°	58.8	8.0
40°-50°	12.9	1.8
50°-60°	4.6	0.6
60°-70°	2.3	0.3
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	652.1	89.0
0°-40°	710.9	97.1
0°-60°	728.5	99.4
0°-90°	732.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	732.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1712	
5°	1674	153
15°	1135	307
25°	407	191
35°	87	59
45°	15	13
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224721

CATALOG NUMBER: LD2B10D010 EU2B10FL409024 2LBD*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1712.0
2.5°	1704.5
5°	1674.4
7.5°	1598.3
10°	1471.5
12.5°	1319.2
15°	1135.1
17.5°	934.0
20°	734.8
22.5°	557.2
25°	406.9
27.5°	286.6
30°	196.4
32.5°	132.5
35°	87.4
37.5°	52.6
40°	32.9
42.5°	22.6
45°	15.0
47.5°	10.3
50°	7.5
52.5°	6.6
55°	4.7
57.5°	3.8
60°	3.8
62.5°	2.8
65°	1.9
67.5°	1.9
70°	1.9
72.5°	1.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)