

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223709

Luminaire Tested: **LD2B10D010 EU2B10SP159050 2LBDSQLC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223709  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA ( 150)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10SP159050 2LBDSQLC\*MMS  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
SPOT OPTIC  
LENSED SQUARE CAST TRIM WITH MATTE METALLIC SILVER  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 451.0 lumens  
Efficiency: N/A  
Efficacy: 43.8 lumens/watt  
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223709

CATALOG NUMBER: LD2B10D010 EU2B10SP159050 2LBDSQLC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P223709

CATALOG NUMBER: LD2B10D010 EU2B10SP159050 2LBDSQLC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	89	88	87
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2167162
5°	1566617
10°	456096
15°	160043
20°	68508
25°	30815
30°	11942
35°	5911
40°	3944
45°	2575
50°	1446
55°	1081
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223709

CATALOG NUMBER: LD2B10D010 EU2B10SP159050 2LBDSQLC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	285.1	63.2
10°-20°	116.0	25.7
20°-30°	35.6	7.9
30°-40°	8.8	1.9
40°-50°	3.7	0.8
50°-60°	1.6	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	436.7	96.8
0°-40°	445.5	98.8
0°-60°	450.7	99.9
0°-90°	451.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	451.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5595	
5°	4029	285
15°	399	116
25°	72	36
35°	12	9
45°	5	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223709

CATALOG NUMBER: LD2B10D010 EU2B10SP159050 2LBDSQLC\*MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5594.9
1°	5509.4
2°	5300.9
3°	4968.4
4°	4534.1
5°	4029.1
6°	3459.9
7°	2842.1
8°	2215.7
9°	1630.0
10°	1159.6
11°	831.1
12°	624.9
13°	508.8
14°	445.3
15°	399.1
17.5°	246.2
20°	166.2
22.5°	111.3
25°	72.1
27.5°	43.9
30°	26.7
32.5°	17.2
35°	12.5
37.5°	10.2
40°	7.8
42.5°	6.3
45°	4.7
47.5°	3.1
50°	2.4
52.5°	2.4
55°	1.6
57.5°	1.6
60°	0.8
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223709

CATALOG NUMBER: LD2B10D010 EU2B10SP159050 2LBDSQLC\*MMS

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)