

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224967

Luminaire Tested: **LD2B10D010 EU2B10FL409024 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224967
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10FL409024 2LBDL*LI
Description: 1000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 693.8 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224967

CATALOG NUMBER: LD2B10D010 EU2B10FL409024 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P224967

CATALOG NUMBER: LD2B10D010 EU2B10FL409024 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96			96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91			91
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87			87
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83			83
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79			79
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76			76
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73			73
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70			70
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67			67
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65			65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	665538
5°	639540
10°	556746
15°	434735
20°	289121
25°	165571
30°	82297
35°	37829
40°	15169
45°	6957
50°	3194
55°	1823
60°	1007
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224967

CATALOG NUMBER: LD2B10D010 EU2B10FL409024 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.7	21.6
10°-20°	294.0	42.4
20°-30°	181.9	26.2
30°-40°	54.4	7.8
40°-50°	10.9	1.6
50°-60°	2.7	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	625.6	90.2
0°-40°	680.0	98.0
0°-60°	693.6	100.0
0°-90°	693.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	693.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1718	
5°	1645	150
15°	1084	294
25°	387	182
35°	80	54
45°	13	11
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224967

CATALOG NUMBER: LD2B10D010 EU2B10FL409024 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1718.2
1°	1708.9
2°	1700.2
3°	1682.9
4°	1666.9
5°	1644.8
6°	1614.8
7°	1576.8
8°	1528.2
9°	1472.8
10°	1415.5
11°	1356.1
12°	1292.8
13°	1226.8
14°	1156.1
15°	1084.1
17.5°	894.1
20°	701.4
22.5°	530.7
25°	387.4
27.5°	272.0
30°	184.0
32.5°	121.3
35°	80.0
37.5°	50.0
40°	30.0
42.5°	19.3
45°	12.7
47.5°	8.0
50°	5.3
52.5°	4.0
55°	2.7
57.5°	2.0
60°	1.3
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224967

CATALOG NUMBER: LD2B10D010 EU2B10FL409024 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)