

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264301

Luminaire Tested: **LD2B10D010 EU2B1010SP159030D2W 2LBSQC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264301
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP159030D2W 2LBSQC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 599.3 lumens
Efficiency: N/A
Efficacy: 58.2 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264301

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBSQC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P264301

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBSQC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2828344
5°	2267040
10°	989471
15°	306664
20°	106895
25°	47196
30°	21363
35°	11082
40°	6312
45°	3000
50°	1842
55°	1118
60°	592
65°	700
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264301

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBSQC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.6	58.0
10°-20°	190.4	31.8
20°-30°	43.4	7.2
30°-40°	12.5	2.1
40°-50°	3.8	0.6
50°-60°	1.1	0.2
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	581.4	97.0
0°-40°	593.8	99.1
0°-60°	598.8	99.9
0°-90°	599.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	599.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5733	
5°	4578	348
15°	600	190
25°	87	43
35°	18	12
45°	4	4
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264301

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBSQC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	5732.8
1°	5661.4
2°	5513.2
3°	5283.2
4°	4967.0
5°	4577.6
6°	4100.3
7°	3567.0
8°	3010.3
9°	2471.5
10°	1975.1
11°	1555.0
12°	1224.0
13°	963.3
14°	760.9
15°	600.4
16°	473.6
17°	377.0
18°	303.3
19°	246.6
20°	203.6
22.5°	131.6
25°	86.7
26°	73.2
27°	62.2
28°	52.3
29°	43.7
30°	37.5
32.5°	25.8
35°	18.4
37.5°	13.5
40°	9.8
42.5°	6.7
45°	4.3
47.5°	3.1
50°	2.4
52.5°	1.8
55°	1.3
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6



TEST NUMBER: P264301

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBSQC*MMS

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)