

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264300

Luminaire Tested: **LD2B10D010 EU2B1010SP159030D2W 2LBSQC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264300  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B1010SP159030D2W 2LBSQC\*MW  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 520.9 lumens  
Efficiency: N/A  
Efficacy: 50.6 lumens/watt  
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264300

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBSQC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P264300

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBSQC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98			
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96			
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94			
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92			
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90			
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89			
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87			
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86			
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85			
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2458224
5°	1970338
10°	860020
15°	266518
20°	92877
25°	41045
30°	18572
35°	9697
40°	5539
45°	2651
50°	1612
55°	860
60°	493
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264300

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBSQC\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	302.1	58.0
10°-20°	165.5	31.8
20°-30°	37.7	7.2
30°-40°	10.9	2.1
40°-50°	3.3	0.6
50°-60°	1.0	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	505.3	97.0
0°-40°	516.2	99.1
0°-60°	520.5	99.9
0°-90°	520.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	520.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4983	
5°	3978	302
15°	522	165
25°	75	38
35°	16	11
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264300

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBSQC\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4982.6
1°	4920.6
2°	4791.7
3°	4591.8
4°	4317.0
5°	3978.5
6°	3563.7
7°	3100.2
8°	2616.4
9°	2148.1
10°	1716.7
11°	1351.5
12°	1063.9
13°	837.2
14°	661.3
15°	521.8
16°	411.7
17°	327.7
18°	263.6
19°	214.4
20°	176.9
22.5°	114.4
25°	75.4
26°	63.6
27°	54.0
28°	45.4
29°	38.0
30°	32.6
32.5°	22.4
35°	16.1
37.5°	11.8
40°	8.6
42.5°	5.8
45°	3.8
47.5°	2.7
50°	2.1
52.5°	1.6
55°	1.0
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5



TEST NUMBER: P264300

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBSQC\*MW

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)