

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P263929

Luminaire Tested: **LD2B10D010 EU2B1010SP158027 2LBD*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P263929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP158027 2LBD*WH
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 945.0 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P263929

CATALOG NUMBER: LD2B10D010 EU2B1010SP158027 2LBD*WH

Luminous Intensity Polar Plot





TEST NUMBER: P263929

CATALOG NUMBER: LD2B10D010 EU2B1010SP158027 2LBD*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	98	98	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	96	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94	94	94	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92	92	92	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90	90	90	90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89	89	89	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87	87	87	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86	86	86	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85	85	85	85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83	83	83	83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4459103
5°	3574193
10°	1559979
15°	483440
20°	168533
25°	74415
30°	33725
35°	17526
40°	9983
45°	4744
50°	2993
55°	1634
60°	987
65°	1167
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P263929

CATALOG NUMBER: LD2B10D010 EU2B1010SP158027 2LBD*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	548.0	58.0
10°-20°	300.1	31.8
20°-30°	68.4	7.2
30°-40°	19.7	2.1
40°-50°	6.1	0.6
50°-60°	1.8	0.2
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	916.6	97.0
0°-40°	936.3	99.1
0°-60°	944.2	99.9
0°-90°	945.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	945.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9038	
5°	7217	548
15°	946	300
25°	137	68
35°	29	20
45°	7	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P263929

CATALOG NUMBER: LD2B10D010 EU2B1010SP158027 2LBD*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	9038.2
1°	8925.7
2°	8692.0
3°	8329.3
4°	7830.8
5°	7217.0
6°	6464.4
7°	5623.6
8°	4746.0
9°	3896.5
10°	3113.9
11°	2451.6
12°	1929.8
13°	1518.6
14°	1199.6
15°	946.5
16°	746.7
17°	594.5
18°	478.1
19°	388.9
20°	321.0
22.5°	207.5
25°	136.7
26°	115.4
27°	97.9
28°	82.4
29°	68.9
30°	59.2
32.5°	40.7
35°	29.1
37.5°	21.3
40°	15.5
42.5°	10.7
45°	6.8
47.5°	4.8
50°	3.9
52.5°	2.9
55°	1.9
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0



TEST NUMBER: P263929

CATALOG NUMBER: LD2B10D010 EU2B1010SP158027 2LBD*WH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)