

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222798

Luminaire Tested: **LD2B10D010 EU2B10NFL259030D2W 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222798
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10NFL259030D2W 2LBD*MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 605.2 lumens
Efficiency: N/A
Efficacy: 58.8 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222798

CATALOG NUMBER: LD2B10D010 EU2B10NFL259030D2W 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P222798

CATALOG NUMBER: LD2B10D010 EU2B10NFL259030D2W 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1390688
5°	1284058
10°	869162
15°	295705
20°	108616
25°	57569
30°	29564
35°	13808
40°	4551
45°	2246
50°	1085
55°	405
60°	465
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222798

CATALOG NUMBER: LD2B10D010 EU2B10NFL259030D2W 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	280.9	46.4
10°-20°	236.2	39.0
20°-30°	64.8	10.7
30°-40°	18.9	3.1
40°-50°	3.5	0.6
50°-60°	0.8	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	581.9	96.2
0°-40°	600.8	99.3
0°-60°	605.1	100.0
0°-90°	605.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	605.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3590	
5°	3302	281
15°	737	236
25°	135	65
35°	29	19
45°	4	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222798

CATALOG NUMBER: LD2B10D010 EU2B10NFL259030D2W 2LBD*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3590.3
1°	3569.5
2°	3532.5
3°	3479.4
4°	3406.8
5°	3302.4
6°	3159.9
7°	2981.7
8°	2764.1
9°	2507.2
10°	2209.8
11°	1883.7
12°	1544.5
13°	1220.8
14°	944.8
15°	737.4
17.5°	416.1
20°	263.5
22.5°	187.8
25°	134.7
27.5°	95.4
30°	66.1
32.5°	46.5
35°	29.2
37.5°	11.9
40°	9.0
42.5°	6.6
45°	4.1
47.5°	2.4
50°	1.8
52.5°	1.2
55°	0.6
57.5°	0.6
60°	0.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222798

CATALOG NUMBER: LD2B10D010 EU2B10NFL259030D2W 2LBD*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)