

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B10D010 EU2B10WFL559030D2W 2LBD*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14806)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10WFL559030D2W 2LBD*GPH
Description: 1000 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 564.7 lumens
Efficiency: N/A
Efficacy: 54.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559030D2W 2LBD*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559030D2W 2LBD*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93				93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86				86
3	102	95	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80				80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74				74
5	92	83	77	73	90	82	77	72	80	75	72	79	74	71	77	73	70	69				69
6	87	78	72	67	85	77	71	67	75	70	67	74	70	66	73	69	66	64				64
7	83	73	67	63	81	72	67	62	71	66	62	70	65	62	69	65	61	60				60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56				56
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53				53
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	269051
5°	266112
10°	245944
15°	215383
20°	185698
25°	158519
30°	125414
35°	86770
40°	56177
45°	34073
50°	19946
55°	11210
60°	4261
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559030D2W 2LBD*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.4	11.2
10°-20°	149.7	26.5
20°-30°	168.5	29.8
30°-40°	116.2	20.6
40°-50°	50.2	8.9
50°-60°	15.6	2.8
60°-70°	1.0	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	381.7	67.6
0°-40°	497.9	88.2
0°-60°	563.7	99.8
0°-90°	564.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	564.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	695	
5°	684	63
15°	537	150
25°	371	169
35°	184	116
45°	62	50
55°	17	16
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559030D2W 2LBD*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	694.6
2.5°	693.1
5°	684.4
7.5°	661.6
10°	625.3
12.5°	582.8
15°	537.1
17.5°	491.5
20°	450.5
22.5°	411.1
25°	370.9
27.5°	328.5
30°	280.4
32.5°	230.0
35°	183.5
37.5°	144.1
40°	111.1
42.5°	83.5
45°	62.2
47.5°	45.7
50°	33.1
52.5°	23.6
55°	16.6
57.5°	11.0
60°	5.5
62.5°	1.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)