

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B10D010 EU2B10WFL559030D2W 2LBDSQC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10WFL559030D2W 2LBDSQC*MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 556.8 lumens
Efficiency: N/A
Efficacy: 54.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LD2B10D010 EU2B10WFL559030D2W 2LBDSQC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559030D2W 2LBDSQC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93			
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80			
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74			
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60			
8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56			
9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53			
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	261187
5°	259502
10°	241263
15°	211814
20°	182566
25°	156125
30°	123893
35°	86392
40°	54660
45°	33360
50°	19705
55°	10805
60°	2324
65°	2108
70°	1812
75°	2395
80°	1561
85°	3111



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559030D2W 2LBDSQC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.9	11.1
10°-20°	147.1	26.4
20°-30°	166.0	29.8
30°-40°	114.8	20.6
40°-50°	49.0	8.8
50°-60°	14.2	2.5
60°-70°	2.1	0.4
70°-80°	1.3	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	375.0	67.3
0°-40°	489.8	88.0
0°-60°	552.9	99.3
0°-90°	556.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	556.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	674	
5°	667	62
15°	528	147
25°	365	166
35°	183	115
45°	61	49
55°	16	14
65°	2	2
75°	2	1
85°	1	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559030D2W 2LBDSQC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	674.3
2.5°	673.6
5°	667.4
7.5°	646.9
10°	613.4
12.5°	572.3
15°	528.2
17.5°	482.5
20°	442.9
22.5°	405.6
25°	365.3
27.5°	322.7
30°	277.0
32.5°	227.5
35°	182.7
37.5°	141.5
40°	108.1
42.5°	81.5
45°	60.9
47.5°	44.2
50°	32.7
52.5°	23.6
55°	16.0
57.5°	6.9
60°	3.0
62.5°	2.3
65°	2.3
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)