

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264915

Luminaire Tested: **LD2B10D010 EU2B1010SP159027 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP159027 2LBDL*MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 745.0 lumens
Efficiency: N/A
Efficacy: 72.3 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264915

CATALOG NUMBER: LD2B10D010 EU2B1010SP159027 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P264915

CATALOG NUMBER: LD2B10D010 EU2B1010SP159027 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83	83	83	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79	79	79	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78	78	78	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2630013
5°	2140554
10°	1156295
15°	461017
20°	184861
25°	88514
30°	45917
35°	24272
40°	13460
45°	8303
50°	5757
55°	3871
60°	2960
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264915

CATALOG NUMBER: LD2B10D010 EU2B1010SP159027 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.6	46.7
10°-20°	274.2	36.8
20°-30°	80.9	10.9
30°-40°	26.9	3.6
40°-50°	10.1	1.4
50°-60°	4.5	0.6
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	702.7	94.3
0°-40°	729.7	97.9
0°-60°	744.3	99.9
0°-90°	745.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	745.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5331	
5°	4322	348
15°	903	274
25°	163	81
35°	40	27
45°	12	10
55°	4	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264915

CATALOG NUMBER: LD2B10D010 EU2B1010SP159027 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5330.8
2.5°	5115.9
5°	4322.2
7.5°	3330.1
10°	2308.1
12.5°	1477.0
15°	902.6
17.5°	550.5
20°	352.1
22.5°	235.7
25°	162.6
27.5°	114.9
30°	80.6
32.5°	56.7
35°	40.3
37.5°	28.3
40°	20.9
42.5°	16.4
45°	11.9
47.5°	10.4
50°	7.5
52.5°	6.0
55°	4.5
57.5°	4.5
60°	3.0
62.5°	1.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)