

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264884

Luminaire Tested: **LD2B15D010 EU2B1510SP159024 2LBSQLC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264884  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B15D010 EU2B1510SP159024 2LBSQLC\*MB  
Description: 1500 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 889.0 lumens  
Efficiency: N/A  
Efficacy: 62.2 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264884

CATALOG NUMBER: LD2B15D010 EU2B1510SP159024 2LBSQLC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P264884

CATALOG NUMBER: LD2B15D010 EU2B1510SP159024 2LBSQLC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83	83	83	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79	79	79	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78	78	78	78

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3138373
5°	2554283
10°	1379779
15°	550146
20°	220615
25°	105661
30°	54747
35°	28970
40°	16037
45°	9908
50°	6831
55°	4559
60°	3552
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264884

CATALOG NUMBER: LD2B15D010 EU2B1510SP159024 2LBSQLC\*MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	414.8	46.7
10°-20°	327.3	36.8
20°-30°	96.5	10.9
30°-40°	32.1	3.6
40°-50°	12.1	1.4
50°-60°	5.3	0.6
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	838.6	94.3
0°-40°	870.7	97.9
0°-60°	888.1	99.9
0°-90°	889.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	889.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6361	
5°	5158	415
15°	1077	327
25°	194	97
35°	48	32
45°	14	12
55°	5	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264884

CATALOG NUMBER: LD2B15D010 EU2B1510SP159024 2LBSQLC\*MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6361.2
2.5°	6104.8
5°	5157.6
7.5°	3973.7
10°	2754.2
12.5°	1762.5
15°	1077.1
17.5°	656.9
20°	420.2
22.5°	281.3
25°	194.1
27.5°	137.1
30°	96.1
32.5°	67.7
35°	48.1
37.5°	33.8
40°	24.9
42.5°	19.6
45°	14.2
47.5°	12.5
50°	8.9
52.5°	7.1
55°	5.3
57.5°	5.3
60°	3.6
62.5°	1.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)