

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264247

Luminaire Tested: **LD2B10D010 EU2B1010SP159027 2LBSQC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264247
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP159027 2LBSQC*MB
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 736.1 lumens
Efficiency: N/A
Efficacy: 71.5 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264247

CATALOG NUMBER: LD2B10D010 EU2B1010SP159027 2LBSQC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P264247

CATALOG NUMBER: LD2B10D010 EU2B1010SP159027 2LBSQC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	98	98	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	96	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94	94	94	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92	92	92	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90	90	90	90
6	103	98	94	92	102	97	94	91	96	93	91	94	92	90	93	91	90	89	89	89	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87	87	87	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86	86	86	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85	85	85	85
10	95	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	83	83	83	83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3472872
5°	2783681
10°	1214959
15°	376536
20°	131256
25°	57975
30°	26262
35°	13672
40°	7793
45°	3698
50°	2303
55°	1290
60°	789
65°	934
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264247

CATALOG NUMBER: LD2B10D010 EU2B1010SP159027 2LBSQC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	426.8	58.0
10°-20°	233.8	31.8
20°-30°	53.3	7.2
30°-40°	15.3	2.1
40°-50°	4.7	0.6
50°-60°	1.4	0.2
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	713.9	97.0
0°-40°	729.2	99.1
0°-60°	735.4	99.9
0°-90°	736.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	736.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7039	
5°	5621	427
15°	737	234
25°	106	53
35°	23	15
45°	5	5
55°	2	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264247

CATALOG NUMBER: LD2B10D010 EU2B1010SP159027 2LBSQC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	7039.2
1°	6951.6
2°	6769.6
3°	6487.1
4°	6098.9
5°	5620.8
6°	5034.7
7°	4379.9
8°	3696.4
9°	3034.7
10°	2425.2
11°	1909.4
12°	1503.0
13°	1182.8
14°	934.3
15°	737.2
16°	581.6
17°	463.0
18°	372.4
19°	302.9
20°	250.0
22.5°	161.6
25°	106.5
26°	89.9
27°	76.3
28°	64.2
29°	53.6
30°	46.1
32.5°	31.7
35°	22.7
37.5°	16.6
40°	12.1
42.5°	8.3
45°	5.3
47.5°	3.8
50°	3.0
52.5°	2.3
55°	1.5
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8



TEST NUMBER: P264247

CATALOG NUMBER: LD2B10D010 EU2B1010SP159027 2LBSQC*MB

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)