

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224823

Luminaire Tested: **LD2B10D010 EU2B10FL409027 2LBDL*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224823
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10FL409027 2LBDL*B
Description: 1000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 731.1 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224823

CATALOG NUMBER: LD2B10D010 EU2B10FL409027 2LBDL*B

Luminous Intensity Polar Plot





TEST NUMBER: P224823

CATALOG NUMBER: LD2B10D010 EU2B10FL409027 2LBDL*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	103	100	108	104	101	99	101	99	96	98	96	94	96	94	92	91			
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87			
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83			
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79			
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76			
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72			
8	87	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	69			
9	84	77	72	69	83	76	72	68	75	71	68	74	71	68	74	70	68	67			
10	82	74	69	66	81	73	69	66	73	68	66	72	68	65	71	68	65	64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	661509
5°	650000
10°	579834
15°	458314
20°	305609
25°	177281
30°	88738
35°	41754
40°	16332
45°	7286
50°	3435
55°	1891
60°	697
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224823

CATALOG NUMBER: LD2B10D010 EU2B10FL409027 2LBDL*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.2	21.0
10°-20°	309.4	42.3
20°-30°	194.6	26.6
30°-40°	59.5	8.1
40°-50°	11.7	1.6
50°-60°	2.6	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	657.2	89.9
0°-40°	716.7	98.0
0°-60°	731.0	100.0
0°-90°	731.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	731.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1708	
5°	1672	153
15°	1143	309
25°	415	195
35°	88	59
45°	13	12
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224823

CATALOG NUMBER: LD2B10D010 EU2B10FL409027 2LBDL*B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1707.8
2.5°	1704.0
5°	1671.7
7.5°	1595.7
10°	1474.2
12.5°	1322.4
15°	1142.9
17.5°	943.6
20°	741.4
22.5°	568.6
25°	414.8
27.5°	292.4
30°	198.4
32.5°	133.8
35°	88.3
37.5°	54.1
40°	32.3
42.5°	20.9
45°	13.3
47.5°	8.5
50°	5.7
52.5°	3.8
55°	2.8
57.5°	1.9
60°	0.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)