

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P263950

Luminaire Tested: **LD2B15D010 EU2B1510SP158027 2LBSQC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P263950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP158027 2LBSQC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1326.0 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P263950

CATALOG NUMBER: LD2B15D010 EU2B1510SP158027 2LBSQC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P263950

CATALOG NUMBER: LD2B15D010 EU2B1510SP158027 2LBSQC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98			98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96			96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94			94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92			92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90			90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89			89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87			87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86			86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85			85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83			83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6256864
5°	5015211
10°	2188900
15°	678348
20°	236471
25°	104464
30°	47284
35°	24573
40°	14040
45°	6628
50°	4145
55°	2322
60°	1381
65°	1634
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P263950

CATALOG NUMBER: LD2B15D010 EU2B1510SP158027 2LBSQC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	769.0	58.0
10°-20°	421.1	31.8
20°-30°	96.0	7.2
30°-40°	27.6	2.1
40°-50°	8.5	0.6
50°-60°	2.6	0.2
60°-70°	1.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1286.1	97.0
0°-40°	1313.7	99.1
0°-60°	1324.8	99.9
0°-90°	1326.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1326.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12682	
5°	10127	769
15°	1328	421
25°	192	96
35°	41	28
45°	10	9
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P263950

CATALOG NUMBER: LD2B15D010 EU2B1510SP158027 2LBSQC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	12682.1
1°	12524.3
2°	12196.3
3°	11687.4
4°	10988.0
5°	10126.7
6°	9070.7
7°	7890.9
8°	6659.5
9°	5467.5
10°	4369.3
11°	3440.0
12°	2707.9
13°	2130.9
14°	1683.2
15°	1328.1
16°	1047.8
17°	834.1
18°	670.8
19°	545.7
20°	450.4
22.5°	291.2
25°	191.9
26°	161.9
27°	137.4
28°	115.7
29°	96.6
30°	83.0
32.5°	57.2
35°	40.8
37.5°	29.9
40°	21.8
42.5°	15.0
45°	9.5
47.5°	6.8
50°	5.4
52.5°	4.1
55°	2.7
57.5°	1.4
60°	1.4
62.5°	1.4
65°	1.4
67.5°	1.4



TEST NUMBER: P263950

CATALOG NUMBER: LD2B15D010 EU2B1510SP158027 2LBSQC*MMS

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)