

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264498

Luminaire Tested: **LD2B10D010 EU2B1010SP159727 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264498
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP159727 2LBD*H
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 640.0 lumens
Efficiency: N/A
Efficacy: 62.1 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264498

CATALOG NUMBER: LD2B10D010 EU2B1010SP159727 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P264498

CATALOG NUMBER: LD2B10D010 EU2B1010SP159727 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	98	98	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	96	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94	94	94	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92	92	92	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90	90	90	90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89	89	89	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87	87	87	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86	86	86	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85	85	85	85
10	95	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	83	83	83	83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3019917
5°	2420616
10°	1056501
15°	327401
20°	114140
25°	50408
30°	22844
35°	11865
40°	6762
45°	3210
50°	1996
55°	1118
60°	691
65°	817
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264498

CATALOG NUMBER: LD2B10D010 EU2B1010SP159727 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	371.2	58.0
10°-20°	203.3	31.8
20°-30°	46.3	7.2
30°-40°	13.3	2.1
40°-50°	4.1	0.6
50°-60°	1.2	0.2
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	620.8	97.0
0°-40°	634.1	99.1
0°-60°	639.4	99.9
0°-90°	640.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	640.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6121	
5°	4888	371
15°	641	203
25°	93	46
35°	20	13
45°	5	4
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264498

CATALOG NUMBER: LD2B10D010 EU2B1010SP159727 2LBD*H

CANDELA DISTRIBUTION (FULL):

0°	
0°	6121.1
1°	6044.9
2°	5886.6
3°	5641.0
4°	5303.4
5°	4887.7
6°	4378.0
7°	3808.6
8°	3214.2
9°	2638.9
10°	2108.9
11°	1660.3
12°	1307.0
13°	1028.5
14°	812.4
15°	641.0
16°	505.7
17°	402.6
18°	323.8
19°	263.4
20°	217.4
22.5°	140.5
25°	92.6
26°	78.2
27°	66.3
28°	55.8
29°	46.6
30°	40.1
32.5°	27.6
35°	19.7
37.5°	14.4
40°	10.5
42.5°	7.2
45°	4.6
47.5°	3.3
50°	2.6
52.5°	2.0
55°	1.3
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.7



TEST NUMBER: P264498

CATALOG NUMBER: LD2B10D010 EU2B1010SP159727 2LBD*H

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)