

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264930

Luminaire Tested: **LD2B15D010 EU2B1510SP159027 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP159027 2LBDL*WH
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1036.0 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264930

CATALOG NUMBER: LD2B15D010 EU2B1510SP159027 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P264930

CATALOG NUMBER: LD2B15D010 EU2B1510SP159027 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97									97																		
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94									94																		
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92									92																		
4	106	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89									89																		
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87									87																		
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85									85																		
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83									83																		
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81									81																		
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79									79																		
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78									78																		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3657291
5°	2976678
10°	1607922
15°	641113
20°	257052
25°	123081
30°	63805
35°	33728
40°	18677
45°	11582
50°	7982
55°	5333
60°	4046
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264930

CATALOG NUMBER: LD2B15D010 EU2B1510SP159027 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	483.4	46.7
10°-20°	381.4	36.8
20°-30°	112.5	10.9
30°-40°	37.4	3.6
40°-50°	14.1	1.4
50°-60°	6.2	0.6
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	977.2	94.3
0°-40°	1014.7	97.9
0°-60°	1035.0	99.9
0°-90°	1036.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1036.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7413	
5°	6010	483
15°	1255	381
25°	226	112
35°	56	37
45°	17	14
55°	6	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264930

CATALOG NUMBER: LD2B15D010 EU2B1510SP159027 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7413.0
2.5°	7114.2
5°	6010.5
7.5°	4630.8
10°	3209.6
12.5°	2054.0
15°	1255.2
17.5°	765.6
20°	489.6
22.5°	327.8
25°	226.1
27.5°	159.8
30°	112.0
32.5°	78.8
35°	56.0
37.5°	39.4
40°	29.0
42.5°	22.8
45°	16.6
47.5°	14.5
50°	10.4
52.5°	8.3
55°	6.2
57.5°	6.2
60°	4.1
62.5°	2.1
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)