

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225326

Luminaire Tested: **LD2B10D010 EU2B10FL409727 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225326
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10FL409727 2LBDC*MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 621.7 lumens
Efficiency: N/A
Efficacy: 60.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225326

CATALOG NUMBER: LD2B10D010 EU2B10FL409727 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P225326

CATALOG NUMBER: LD2B10D010 EU2B10FL409727 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86	86	86	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79	79	79	79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	562814
5°	552560
10°	491219
15°	386333
20°	257051
25°	147577
30°	74560
35°	35086
40°	14107
45°	7012
50°	3857
55°	2701
60°	2479
65°	1466
70°	1812
75°	1197
80°	1785
85°	0



TEST NUMBER: P225326

CATALOG NUMBER: LD2B10D010 EU2B10FL409727 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.2	20.9
10°-20°	261.0	42.0
20°-30°	162.3	26.1
30°-40°	49.9	8.0
40°-50°	11.0	1.8
50°-60°	3.9	0.6
60°-70°	2.0	0.3
70°-80°	1.2	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	553.5	89.0
0°-40°	603.4	97.0
0°-60°	618.3	99.4
0°-90°	621.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	621.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1453	
5°	1421	130
15°	963	261
25°	345	162
35°	74	50
45°	13	11
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P225326

CATALOG NUMBER: LD2B10D010 EU2B10FL409727 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1453.0
2.5°	1446.7
5°	1421.1
7.5°	1356.5
10°	1248.9
12.5°	1119.7
15°	963.4
17.5°	792.7
20°	623.6
22.5°	472.9
25°	345.3
27.5°	243.2
30°	166.7
32.5°	112.4
35°	74.2
37.5°	44.7
40°	27.9
42.5°	19.1
45°	12.8
47.5°	8.8
50°	6.4
52.5°	5.6
55°	4.0
57.5°	3.2
60°	3.2
62.5°	2.4
65°	1.6
67.5°	1.6
70°	1.6
72.5°	1.6
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)