

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223640

Luminaire Tested: **LD2B10D010 EU2B10SP159727 2LBDSQC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223640
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10SP159727 2LBDSQC*MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
SPOT OPTIC
SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 392.3 lumens
Efficiency: N/A
Efficacy: 38.1 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223640

CATALOG NUMBER: LD2B10D010 EU2B10SP159727 2LBDSQC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223640

CATALOG NUMBER: LD2B10D010 EU2B10SP159727 2LBDSQC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98				98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96				96
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94				94
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93				93
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91				91
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90				90
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88				88
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87				87
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86				86
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85				85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1885097
5°	1362717
10°	396743
15°	139191
20°	59605
25°	26797
30°	10377
35°	5154
40°	3438
45°	2246
50°	1205
55°	945
60°	542
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223640

CATALOG NUMBER: LD2B10D010 EU2B10SP159727 2LBDSQC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.0	63.2
10°-20°	100.9	25.7
20°-30°	31.0	7.9
30°-40°	7.6	1.9
40°-50°	3.2	0.8
50°-60°	1.4	0.3
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.9	96.8
0°-40°	387.5	98.8
0°-60°	392.0	99.9
0°-90°	392.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	392.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4867	
5°	3505	248
15°	347	101
25°	63	31
35°	11	8
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223640

CATALOG NUMBER: LD2B10D010 EU2B10SP159727 2LBDSQC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4866.7
1°	4792.3
2°	4610.9
3°	4321.8
4°	3943.9
5°	3504.7
6°	3009.6
7°	2472.2
8°	1927.3
9°	1417.9
10°	1008.7
11°	722.9
12°	543.5
13°	442.6
14°	387.4
15°	347.1
17.5°	214.1
20°	144.6
22.5°	96.8
25°	62.7
27.5°	38.2
30°	23.2
32.5°	15.0
35°	10.9
37.5°	8.9
40°	6.8
42.5°	5.5
45°	4.1
47.5°	2.7
50°	2.0
52.5°	2.0
55°	1.4
57.5°	1.4
60°	0.7
62.5°	0.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223640

CATALOG NUMBER: LD2B10D010 EU2B10SP159727 2LBDSQC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)