

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223642

Luminaire Tested: **LD2B10D010 EU2B10SP159727 2LBDSQLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223642
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10SP159727 2LBDSQLC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Downlight
SPOT OPTIC
LENSED SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 356.2 lumens
Efficiency: N/A
Efficacy: 34.6 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223642

CATALOG NUMBER: LD2B10D010 EU2B10SP159727 2LBDSQLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P223642

CATALOG NUMBER: LD2B10D010 EU2B10SP159727 2LBDSQLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																																				
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96																																				
3	110	106	103	101	108	105	102	100	102	100	98	100	99	97	98	97	96	94																																				
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93																																				
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91																																				
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90																																				
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88																																				
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87																																				
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86																																				
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1711604
5°	1237321
10°	360204
15°	126398
20°	54123
25°	24361
30°	9437
35°	4681
40°	3135
45°	2027
50°	1145
55°	810
60°	465
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223642

CATALOG NUMBER: LD2B10D010 EU2B10SP159727 2LBDSQLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.2	63.2
10°-20°	91.6	25.7
20°-30°	28.1	7.9
30°-40°	6.9	1.9
40°-50°	2.9	0.8
50°-60°	1.2	0.3
60°-70°	0.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	344.9	96.8
0°-40°	351.8	98.8
0°-60°	356.0	99.9
0°-90°	356.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	356.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4419	
5°	3182	225
15°	315	92
25°	57	28
35°	10	7
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223642

CATALOG NUMBER: LD2B10D010 EU2B10SP159727 2LBDSQLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	4418.8
1°	4351.3
2°	4186.6
3°	3924.1
4°	3581.0
5°	3182.2
6°	2732.7
7°	2244.7
8°	1749.9
9°	1287.4
10°	915.8
11°	656.4
12°	493.5
13°	401.9
14°	351.7
15°	315.2
17.5°	194.4
20°	131.3
22.5°	87.9
25°	57.0
27.5°	34.7
30°	21.1
32.5°	13.6
35°	9.9
37.5°	8.0
40°	6.2
42.5°	5.0
45°	3.7
47.5°	2.5
50°	1.9
52.5°	1.9
55°	1.2
57.5°	1.2
60°	0.6
62.5°	0.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223642

CATALOG NUMBER: LD2B10D010 EU2B10SP159727 2LBDSQLC*MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)