

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265191

Luminaire Tested: **LD2B15D010 EU2B1510SP159727 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265191
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP159727 2LBDL*WMH
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 855.0 lumens
Efficiency: N/A
Efficacy: 59.8 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265191

CATALOG NUMBER: LD2B15D010 EU2B1510SP159727 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P265191

CATALOG NUMBER: LD2B15D010 EU2B1510SP159727 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92
4	106	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	79	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3018338
5°	2456620
10°	1327027
15°	529102
20°	212162
25°	101578
30°	52696
35°	27825
40°	15457
45°	9559
50°	6601
55°	4387
60°	3355
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265191

CATALOG NUMBER: LD2B15D010 EU2B1510SP159727 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	398.9	46.7
10°-20°	314.7	36.8
20°-30°	92.8	10.9
30°-40°	30.9	3.6
40°-50°	11.6	1.4
50°-60°	5.1	0.6
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	806.5	94.3
0°-40°	837.4	97.9
0°-60°	854.1	99.9
0°-90°	855.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	855.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6118	
5°	4960	399
15°	1036	315
25°	187	93
35°	46	31
45°	14	12
55°	5	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265191

CATALOG NUMBER: LD2B15D010 EU2B1510SP159727 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	6117.9
2.5°	5871.3
5°	4960.4
7.5°	3821.7
10°	2648.9
12.5°	1695.1
15°	1035.9
17.5°	631.8
20°	404.1
22.5°	270.5
25°	186.6
27.5°	131.8
30°	92.5
32.5°	65.1
35°	46.2
37.5°	32.5
40°	24.0
42.5°	18.8
45°	13.7
47.5°	12.0
50°	8.6
52.5°	6.8
55°	5.1
57.5°	5.1
60°	3.4
62.5°	1.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)