

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265198

Luminaire Tested: **LD2B15D010 EU2B1510SP159727 2LBSQLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP159727 2LBSQLC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 812.0 lumens
Efficiency: N/A
Efficacy: 56.8 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265198

CATALOG NUMBER: LD2B15D010 EU2B1510SP159727 2LBSQLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P265198

CATALOG NUMBER: LD2B15D010 EU2B1510SP159727 2LBSQLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97		
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94		
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92		
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89		
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87		
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85		
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83		
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81		
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79		
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2866531
5°	2333056
10°	1260247
15°	502491
20°	201504
25°	96461
30°	50018
35°	26440
40°	14684
45°	9070
50°	6217
55°	4215
60°	3256
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265198

CATALOG NUMBER: LD2B15D010 EU2B1510SP159727 2LBSQLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	378.9	46.7
10°-20°	298.9	36.8
20°-30°	88.2	10.9
30°-40°	29.4	3.6
40°-50°	11.0	1.4
50°-60°	4.9	0.6
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	765.9	94.3
0°-40°	795.3	97.9
0°-60°	811.2	99.9
0°-90°	812.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	812.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5810	
5°	4711	379
15°	984	299
25°	177	88
35°	44	29
45°	13	11
55°	5	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265198

CATALOG NUMBER: LD2B15D010 EU2B1510SP159727 2LBSQLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	5810.2
2.5°	5576.0
5°	4710.9
7.5°	3629.5
10°	2515.6
12.5°	1609.9
15°	983.8
17.5°	600.0
20°	383.8
22.5°	256.9
25°	177.2
27.5°	125.2
30°	87.8
32.5°	61.8
35°	43.9
37.5°	30.9
40°	22.8
42.5°	17.9
45°	13.0
47.5°	11.4
50°	8.1
52.5°	6.5
55°	4.9
57.5°	4.9
60°	3.3
62.5°	1.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)