

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P263985

Luminaire Tested: **LD2B10D010 EU2B1010SP158030 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P263985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP158030 2LBDC*MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 964.0 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P263985

CATALOG NUMBER: LD2B10D010 EU2B1010SP158030 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P263985

CATALOG NUMBER: LD2B10D010 EU2B1010SP158030 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98			98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96			96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94			94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92			92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90			90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89			89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87			87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86			86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85			85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83			83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4548746
5°	3646053
10°	1591340
15°	493144
20°	171893
25°	75939
30°	34352
35°	17888
40°	10176
45°	4814
50°	3070
55°	1720
60°	987
65°	1167
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P263985

CATALOG NUMBER: LD2B10D010 EU2B1010SP158030 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	559.1	58.0
10°-20°	306.2	31.8
20°-30°	69.8	7.2
30°-40°	20.1	2.1
40°-50°	6.2	0.6
50°-60°	1.9	0.2
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.0	97.0
0°-40°	955.1	99.1
0°-60°	963.1	99.9
0°-90°	964.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	964.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9220	
5°	7362	559
15°	966	306
25°	140	70
35°	30	20
45°	7	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P263985

CATALOG NUMBER: LD2B10D010 EU2B1010SP158030 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9219.9
1°	9105.1
2°	8866.7
3°	8496.7
4°	7988.3
5°	7362.1
6°	6594.4
7°	5736.7
8°	4841.4
9°	3974.8
10°	3176.5
11°	2500.8
12°	1968.6
13°	1549.2
14°	1223.7
15°	965.5
16°	761.7
17°	606.4
18°	487.7
19°	396.7
20°	327.4
22.5°	211.7
25°	139.5
26°	117.7
27°	99.9
28°	84.1
29°	70.2
30°	60.3
32.5°	41.5
35°	29.7
37.5°	21.8
40°	15.8
42.5°	10.9
45°	6.9
47.5°	4.9
50°	4.0
52.5°	3.0
55°	2.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0



TEST NUMBER: P263985

CATALOG NUMBER: LD2B10D010 EU2B1010SP158030 2LBDC*MW

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)