

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B15D010 EU2B15WFL559727 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14811)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15WFL559727 2LBDC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 901.5 lumens
Efficiency: N/A
Efficacy: 63.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LD2B15D010 EU2B15WFL559727 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL559727 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	84	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75		
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69		
6	87	78	72	68	86	77	72	67	76	71	67	74	70	66	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	62	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	430380
5°	426269
10°	395642
15°	347315
20°	298890
25°	254382
30°	201450
35°	139825
40°	88842
45°	53519
50°	30552
55°	16680
60°	1937
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL559727 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.7	11.3
10°-20°	241.1	26.7
20°-30°	270.6	30.0
30°-40°	186.5	20.7
40°-50°	78.8	8.7
50°-60°	22.2	2.5
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	613.4	68.0
0°-40°	799.9	88.7
0°-60°	900.9	99.9
0°-90°	901.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	901.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1111	
5°	1096	102
15°	866	241
25°	595	271
35°	296	186
45°	98	79
55°	25	22
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL559727 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1111.1
2.5°	1107.4
5°	1096.3
7.5°	1061.6
10°	1005.9
12.5°	937.9
15°	866.1
17.5°	790.6
20°	725.1
22.5°	662.0
25°	595.2
27.5°	525.9
30°	450.4
32.5°	368.7
35°	295.7
37.5°	231.4
40°	175.7
42.5°	132.4
45°	97.7
47.5°	70.5
50°	50.7
52.5°	37.1
55°	24.7
57.5°	12.4
60°	2.5
62.5°	1.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)