

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P263987

Luminaire Tested: **LD2B10D010 EU2B1010SP158030 2LBSQC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P263987  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B1010SP158030 2LBSQC\*MB  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 952.0 lumens  
Efficiency: N/A  
Efficacy: 92.4 lumens/watt  
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P263987

CATALOG NUMBER: LD2B10D010 EU2B1010SP158030 2LBSQC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P263987

CATALOG NUMBER: LD2B10D010 EU2B1010SP158030 2LBSQC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0										
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							100												
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	97	96	95	94	93	92	91	90	89										
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	95	94	93	92	91	90	89	88	87										
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94	93	92	91	90	89	88	87	86	85										
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92	91	90	89	88	87	86	85	84	83										
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90	89	88	87	86	85	84	83	82	81										
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89	88	87	86	85	84	83	82	81	80										
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87	86	85	84	83	82	81	80	79	78										
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86	85	84	83	82	81	80	79	78	77										
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	84	83	82	81	80	79	78	77	76	75										
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83	82	81	80	79	78	77	76	75	74										

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4492108
5°	3600639
10°	1571551
15°	487015
20°	169793
25°	74959
30°	33953
35°	17647
40°	10047
45°	4744
50°	2993
55°	1720
60°	987
65°	1167
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P263987

CATALOG NUMBER: LD2B10D010 EU2B1010SP158030 2LBSQC\*MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	552.1	58.0
10°-20°	302.4	31.8
20°-30°	68.9	7.2
30°-40°	19.8	2.1
40°-50°	6.1	0.6
50°-60°	1.8	0.2
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	923.4	97.0
0°-40°	943.2	99.1
0°-60°	951.1	99.9
0°-90°	952.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	952.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9105	
5°	7270	552
15°	954	302
25°	138	69
35°	29	20
45°	7	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P263987

CATALOG NUMBER: LD2B10D010 EU2B1010SP158030 2LBSQC\*MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9105.1
1°	8991.8
2°	8756.3
3°	8391.0
4°	7888.8
5°	7270.4
6°	6512.3
7°	5665.3
8°	4781.2
9°	3925.4
10°	3137.0
11°	2469.7
12°	1944.1
13°	1529.9
14°	1208.5
15°	953.5
16°	752.2
17°	598.9
18°	481.6
19°	391.8
20°	323.4
22.5°	209.1
25°	137.7
26°	116.3
27°	98.7
28°	83.0
29°	69.4
30°	59.6
32.5°	41.0
35°	29.3
37.5°	21.5
40°	15.6
42.5°	10.7
45°	6.8
47.5°	4.9
50°	3.9
52.5°	2.9
55°	2.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0



TEST NUMBER: P263987

CATALOG NUMBER: LD2B10D010 EU2B1010SP158030 2LBSQC\*MB

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)