

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P263994

Luminaire Tested: **LD2B15D010 EU2B1510SP158030 2LBD*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P263994
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP158030 2LBD*WH
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1297.0 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P263994

CATALOG NUMBER: LD2B15D010 EU2B1510SP158030 2LBD*WH

Luminous Intensity Polar Plot





TEST NUMBER: P263994

CATALOG NUMBER: LD2B15D010 EU2B1510SP158030 2LBD*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	98	98	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	96	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94	94	94	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92	92	92	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90	90	90	90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89	89	89	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87	87	87	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86	86	86	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85	85	85	85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83	83	83	83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6120054
5°	4905514
10°	2141057
15°	663485
20°	231326
25°	102177
30°	46258
35°	24031
40°	13718
45°	6489
50°	4068
55°	2322
60°	1283
65°	1518
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P263994

CATALOG NUMBER: LD2B15D010 EU2B1510SP158030 2LBD*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	752.2	58.0
10°-20°	411.9	31.8
20°-30°	93.9	7.2
30°-40°	27.0	2.1
40°-50°	8.3	0.6
50°-60°	2.5	0.2
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1258.0	97.0
0°-40°	1285.0	99.1
0°-60°	1295.8	99.9
0°-90°	1297.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1297.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12405	
5°	9905	752
15°	1299	412
25°	188	94
35°	40	27
45°	9	8
55°	3	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P263994

CATALOG NUMBER: LD2B15D010 EU2B1510SP158030 2LBD*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	12404.8
1°	12250.4
2°	11929.6
3°	11431.8
4°	10747.7
5°	9905.2
6°	8872.3
7°	7718.4
8°	6513.8
9°	5347.9
10°	4273.8
11°	3364.7
12°	2648.7
13°	2084.3
14°	1646.4
15°	1299.0
16°	1024.9
17°	815.9
18°	656.2
19°	533.7
20°	440.6
22.5°	284.8
25°	187.7
26°	158.4
27°	134.4
28°	113.1
29°	94.5
30°	81.2
32.5°	55.9
35°	39.9
37.5°	29.3
40°	21.3
42.5°	14.6
45°	9.3
47.5°	6.7
50°	5.3
52.5°	4.0
55°	2.7
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	1.3



TEST NUMBER: P263994

CATALOG NUMBER: LD2B15D010 EU2B1510SP158030 2LBD*WH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)