

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225301

Luminaire Tested: **LD2B15D010 EU2B15FL408030 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225301
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL408030 2LBDC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1382.8 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225301

CATALOG NUMBER: LD2B15D010 EU2B15FL408030 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P225301

CATALOG NUMBER: LD2B15D010 EU2B15FL408030 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1251863
5°	1229039
10°	1092568
15°	859284
20°	571770
25°	328277
30°	165802
35°	78022
40°	31401
45°	15557
50°	8557
55°	6010
60°	5500
65°	3208
70°	3964
75°	2694
80°	4015
85°	0



TEST NUMBER: P225301

CATALOG NUMBER: LD2B15D010 EU2B15FL408030 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.5	20.9
10°-20°	580.4	42.0
20°-30°	361.1	26.1
30°-40°	111.0	8.0
40°-50°	24.4	1.8
50°-60°	8.7	0.6
60°-70°	4.3	0.3
70°-80°	2.6	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1231.0	89.0
0°-40°	1342.0	97.1
0°-60°	1375.1	99.4
0°-90°	1382.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1382.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3232	
5°	3161	289
15°	2143	580
25°	768	361
35°	165	111
45°	28	24
55°	9	9
65°	4	4
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P225301

CATALOG NUMBER: LD2B15D010 EU2B15FL408030 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3231.9
2.5°	3217.7
5°	3160.9
7.5°	3017.3
10°	2777.8
12.5°	2490.4
15°	2142.8
17.5°	1763.2
20°	1387.1
22.5°	1051.9
25°	768.1
27.5°	541.0
30°	370.7
32.5°	250.1
35°	165.0
37.5°	99.3
40°	62.1
42.5°	42.6
45°	28.4
47.5°	19.5
50°	14.2
52.5°	12.4
55°	8.9
57.5°	7.1
60°	7.1
62.5°	5.3
65°	3.5
67.5°	3.5
70°	3.5
72.5°	3.5
75°	1.8
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)