

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223386

Luminaire Tested: **LD2B15D010 EU2B15NFL258030 2LBDSQLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15NFL258030 2LBDSQLC*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1214.0 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223386

CATALOG NUMBER: LD2B15D010 EU2B15NFL258030 2LBDSQLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223386

CATALOG NUMBER: LD2B15D010 EU2B15NFL258030 2LBDSQLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0										
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100										
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97									97										
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95									95										
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92									92										
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90									90										
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88									88										
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86									86										
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84									84										
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82									82										
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80									80										
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79									79										

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2789743
5°	2575814
10°	1743515
15°	593174
20°	217850
25°	115481
30°	59353
35°	27710
40°	9051
45°	4601
50°	2169
55°	810
60°	930
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223386

CATALOG NUMBER: LD2B15D010 EU2B15NFL258030 2LBDSQLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	563.5	46.4
10°-20°	473.8	39.0
20°-30°	130.0	10.7
30°-40°	37.9	3.1
40°-50°	7.0	0.6
50°-60°	1.6	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1167.3	96.2
0°-40°	1205.2	99.3
0°-60°	1213.9	100.0
0°-90°	1214.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1214.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7202	
5°	6625	564
15°	1479	474
25°	270	130
35°	59	38
45°	8	7
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223386

CATALOG NUMBER: LD2B15D010 EU2B15NFL258030 2LBDSQLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7202.2
1°	7160.4
2°	7086.2
3°	6979.8
4°	6833.9
5°	6624.6
6°	6338.8
7°	5981.3
8°	5544.8
9°	5029.5
10°	4432.8
11°	3778.7
12°	3098.3
13°	2449.0
14°	1895.3
15°	1479.2
17.5°	834.7
20°	528.5
22.5°	376.7
25°	270.2
27.5°	191.3
30°	132.7
32.5°	93.3
35°	58.6
37.5°	23.9
40°	17.9
42.5°	13.2
45°	8.4
47.5°	4.8
50°	3.6
52.5°	2.4
55°	1.2
57.5°	1.2
60°	1.2
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223386

CATALOG NUMBER: LD2B15D010 EU2B15NFL258030 2LBDSQLC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)