

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B10D010 EU2B1010NFL259730 2LBPIN**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14816)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010NFL259730 2LBPIN
Description: 1000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
ROUND PINHOLE BLACK OCULUS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 594.7 lumens
Efficiency: N/A
Efficacy: 57.7 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LD2B10D010 EU2B1010NFL259730 2LBPIN

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B1010NFL259730 2LBPIN

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97			97																
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95			95																
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93			93																
4	106	101	98	95	105	100	97	95	98	96	94	97	94	93	95	93	92	90			90																
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	88			88																
6	101	96	92	89	100	95	91	89	94	91	88	92	90	88	91	89	87	86			86																
7	99	93	89	87	98	93	89	87	92	88	86	91	88	86	90	87	85	85			85																
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	85	84	83			83																
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	81			81																
10	93	87	83	81	92	87	83	81	86	83	81	85	83	81	85	82	80	80			80																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1396420
5°	1296772
10°	881357
15°	291599
20°	99047
25°	50194
30°	25906
35°	8515
40°	3187
45°	1699
50°	482
55°	540
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B1010NFL259730 2LBPIN

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.2	47.6
10°-20°	236.6	39.8
20°-30°	57.2	9.6
30°-40°	14.8	2.5
40°-50°	2.4	0.4
50°-60°	0.4	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	577.1	97.0
0°-40°	591.8	99.5
0°-60°	594.7	100.0
0°-90°	594.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	594.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3604	
5°	3334	283
15°	727	237
25°	117	57
35°	18	15
45°	3	2
55°	1	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B1010NFL259730 2LBPIN

CANDELA DISTRIBUTION (FULL):

	0°
0°	3603.8
2.5°	3543.5
5°	3333.9
7.5°	2899.6
10°	2240.0
12.5°	1385.7
15°	726.9
17.5°	392.8
20°	240.2
22.5°	165.9
25°	117.4
27.5°	82.9
30°	57.9
32.5°	40.7
35°	18.0
37.5°	7.8
40°	6.3
42.5°	4.7
45°	3.1
47.5°	1.6
50°	0.8
52.5°	0.8
55°	0.8
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)