

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224974

Luminaire Tested: **LD2B10D010 EU2B10FL409730 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224974
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10FL409730 2LBDL*LI
Description: 1000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 715.1 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224974

CATALOG NUMBER: LD2B10D010 EU2B10FL409730 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P224974

CATALOG NUMBER: LD2B10D010 EU2B10FL409730 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96				96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91				91
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87				87
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83				83
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79				79
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76				76
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73				73
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70				70
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67				67
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65				65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	685951
5°	659176
10°	573817
15°	448089
20°	297983
25°	170656
30°	84847
35°	39011
40°	15624
45°	7176
50°	3314
55°	1823
60°	1085
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224974

CATALOG NUMBER: LD2B10D010 EU2B10FL409730 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.3	21.6
10°-20°	303.0	42.4
20°-30°	187.5	26.2
30°-40°	56.1	7.8
40°-50°	11.2	1.6
50°-60°	2.7	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	644.8	90.2
0°-40°	700.9	98.0
0°-60°	714.9	100.0
0°-90°	715.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	715.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1771	
5°	1695	154
15°	1117	303
25°	399	188
35°	82	56
45°	13	11
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224974

CATALOG NUMBER: LD2B10D010 EU2B10FL409730 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1770.9
1°	1761.3
2°	1752.4
3°	1734.5
4°	1718.0
5°	1695.3
6°	1664.4
7°	1625.3
8°	1575.1
9°	1518.0
10°	1458.9
11°	1397.8
12°	1332.5
13°	1264.5
14°	1191.6
15°	1117.4
17.5°	921.5
20°	722.9
22.5°	547.0
25°	399.3
27.5°	280.4
30°	189.7
32.5°	125.1
35°	82.5
37.5°	51.5
40°	30.9
42.5°	19.9
45°	13.1
47.5°	8.2
50°	5.5
52.5°	4.1
55°	2.7
57.5°	2.1
60°	1.4
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224974

CATALOG NUMBER: LD2B10D010 EU2B10FL409730 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)