

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223600

Luminaire Tested: **LD2B10D010 EU2B10SP159730 2LBDSQC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223600
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10SP159730 2LBDSQC*MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
SPOT OPTIC
SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 416.3 lumens
Efficiency: N/A
Efficacy: 40.4 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223600

CATALOG NUMBER: LD2B10D010 EU2B10SP159730 2LBDSQC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223600

CATALOG NUMBER: LD2B10D010 EU2B10SP159730 2LBDSQC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98				98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96				96
3	110	106	103	101	108	105	102	100	102	100	98	100	99	97	98	97	96	94				94
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93				93
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	96	94	92	91				91
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90				90
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88				88
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87				87
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86				86
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85				85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2000410
5°	1446081
10°	421011
15°	147732
20°	63232
25°	28464
30°	11003
35°	5485
40°	3641
45°	2355
50°	1326
55°	945
60°	542
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223600

CATALOG NUMBER: LD2B10D010 EU2B10SP159730 2LBDSQC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	263.2	63.2
10°-20°	107.1	25.7
20°-30°	32.9	7.9
30°-40°	8.1	1.9
40°-50°	3.4	0.8
50°-60°	1.4	0.3
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	403.1	96.8
0°-40°	411.2	98.8
0°-60°	416.0	99.9
0°-90°	416.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	416.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5164	
5°	3719	263
15°	368	107
25°	67	33
35°	12	8
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223600

CATALOG NUMBER: LD2B10D010 EU2B10SP159730 2LBDSQC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5164.4
1°	5085.5
2°	4893.0
3°	4586.2
4°	4185.2
5°	3719.1
6°	3193.7
7°	2623.4
8°	2045.2
9°	1504.6
10°	1070.4
11°	767.1
12°	576.8
13°	469.7
14°	411.1
15°	368.4
17.5°	227.2
20°	153.4
22.5°	102.8
25°	66.6
27.5°	40.5
30°	24.6
32.5°	15.9
35°	11.6
37.5°	9.4
40°	7.2
42.5°	5.8
45°	4.3
47.5°	2.9
50°	2.2
52.5°	2.2
55°	1.4
57.5°	1.4
60°	0.7
62.5°	0.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223600

CATALOG NUMBER: LD2B10D010 EU2B10SP159730 2LBDSQC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)