

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264039

Luminaire Tested: **LD2B10D010 EU2B1010SP158035 2LBSQC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264039
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP158035 2LBSQC*MB
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 962.0 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264039

CATALOG NUMBER: LD2B10D010 EU2B1010SP158035 2LBSQC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P264039

CATALOG NUMBER: LD2B10D010 EU2B1010SP158035 2LBSQC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																																																																																					
RC	80									70									50									30									10									0																																																																												
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																																																																																												
RCR																																																																																																																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																																																																																								
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	96	94	92	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0																																																							
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	95	94	93	92	91	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75	74	73	72	71	70	69	68	67	66	65	64	63	62	61	60	59	58	57	56	55	54	53	52	51	50	49	48	47	46	45	44	43	42	41	40	39	38	37	36	35	34	33	32	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0								
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	94	92	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0																																																										
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	94	92	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0																																																											
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	89	87	85	83	81	79	77	75	73	71	69	67	65	63	61	59	57	55	53	51	49	47	45	43	41	39	37	35	33	31	29	27	25	23	21	19	17	15	13	11	9	7	5	3	1	0																																																											
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	89	87	85	83	81	79	77	75	73	71	69	67	65	63	61	59	57	55	53	51	49	47	45	43	41	39	37	35	33	31	29	27	25	23	21	19	17	15	13	11	9	7	5	3	1	0																																																												
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0																																																													
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	89	87	85	83	81	79	77	75	73	71	69	67	65	63	61	59	57	55	53	51	49	47	45	43	41	39	37	35	33	31	29	27	25	23	21	19	17	15	13	11	9	7	5	3	1	0																																																													
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	83	81	79	77	75	73	71	69	67	65	63	61	59	57	55	53	51	49	47	45	43	41	39	37	35	33	31	29	27	25	23	21	19	17	15	13	11	9	7	5	3	1	0																																																														
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0																																																															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4539323
5°	3638476
10°	1588033
15°	492123
20°	171578
25°	75776
30°	34295
35°	17828
40°	10176
45°	4814
50°	2993
55°	1720
60°	987
65°	1167
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264039

CATALOG NUMBER: LD2B10D010 EU2B1010SP158035 2LBSQC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	557.9	58.0
10°-20°	305.5	31.8
20°-30°	69.6	7.2
30°-40°	20.0	2.1
40°-50°	6.2	0.6
50°-60°	1.9	0.2
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	933.1	97.0
0°-40°	953.1	99.1
0°-60°	961.2	99.9
0°-90°	962.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	962.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9201	
5°	7347	558
15°	964	306
25°	139	70
35°	30	20
45°	7	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264039

CATALOG NUMBER: LD2B10D010 EU2B1010SP158035 2LBSQC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	9200.8
1°	9086.2
2°	8848.3
3°	8479.1
4°	7971.7
5°	7346.8
6°	6580.7
7°	5724.8
8°	4831.4
9°	3966.6
10°	3169.9
11°	2495.7
12°	1964.5
13°	1546.0
14°	1221.2
15°	963.5
16°	760.1
17°	605.2
18°	486.7
19°	395.9
20°	326.8
22.5°	211.3
25°	139.2
26°	117.5
27°	99.7
28°	83.9
29°	70.1
30°	60.2
32.5°	41.5
35°	29.6
37.5°	21.7
40°	15.8
42.5°	10.9
45°	6.9
47.5°	4.9
50°	3.9
52.5°	3.0
55°	2.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0



TEST NUMBER: P264039

CATALOG NUMBER: LD2B10D010 EU2B1010SP158035 2LBSQC*MB

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)