

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224760

Luminaire Tested: **LD2B10D010 EU2B10FL408035 2LBDL\**MW***

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224760  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10FL408035 2LBDL\*MW  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 968.6 lumens  
Efficiency: N/A  
Efficacy: 94.0 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224760

CATALOG NUMBER: LD2B10D010 EU2B10FL408035 2LBDL\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P224760

CATALOG NUMBER: LD2B10D010 EU2B10FL408035 2LBDL\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86	86	86	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64	64	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	876874
5°	860899
10°	765285
15°	601876
20°	400498
25°	229935
30°	116156
35°	54663
40°	21996
45°	10901
50°	5966
55°	4187
60°	3873
65°	2291
70°	2831
75°	1796
80°	2677
85°	0



TEST NUMBER: P224760

CATALOG NUMBER: LD2B10D010 EU2B10FL408035 2LBDL\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.8	20.9
10°-20°	406.6	42.0
20°-30°	252.9	26.1
30°-40°	77.8	8.0
40°-50°	17.1	1.8
50°-60°	6.1	0.6
60°-70°	3.1	0.3
70°-80°	1.8	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	862.3	89.0
0°-40°	940.1	97.1
0°-60°	963.2	99.4
0°-90°	968.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	968.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2264	
5°	2214	203
15°	1501	407
25°	538	253
35°	116	78
45°	20	17
55°	6	6
65°	2	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P224760

CATALOG NUMBER: LD2B10D010 EU2B10FL408035 2LBDL\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2263.8
2.5°	2253.9
5°	2214.1
7.5°	2113.5
10°	1945.7
12.5°	1744.5
15°	1500.9
17.5°	1235.0
20°	971.6
22.5°	736.8
25°	538.0
27.5°	379.0
30°	259.7
32.5°	175.2
35°	115.6
37.5°	69.6
40°	43.5
42.5°	29.8
45°	19.9
47.5°	13.7
50°	9.9
52.5°	8.7
55°	6.2
57.5°	5.0
60°	5.0
62.5°	3.7
65°	2.5
67.5°	2.5
70°	2.5
72.5°	2.5
75°	1.2
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)