

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224771

Luminaire Tested: **LD2B15D010 EU2B15FL408035 2LBDL\**MW***

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224771  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B15D010 EU2B15FL408035 2LBDL\*MW  
Description: 1500 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1303.8 lumens  
Efficiency: N/A  
Efficacy: 91.2 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224771

CATALOG NUMBER: LD2B15D010 EU2B15FL408035 2LBDL\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P224771

CATALOG NUMBER: LD2B15D010 EU2B15FL408035 2LBDL\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1180359
5°	1158856
10°	1030148
15°	810201
20°	539123
25°	309515
30°	156320
35°	73530
40°	29580
45°	14681
50°	8075
55°	5673
60°	5190
65°	3025
70°	3737
75°	2544
80°	3792
85°	0



TEST NUMBER: P224771

CATALOG NUMBER: LD2B15D010 EU2B15FL408035 2LBDL\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	273.0	20.9
10°-20°	547.3	42.0
20°-30°	340.5	26.1
30°-40°	104.7	8.0
40°-50°	23.0	1.8
50°-60°	8.2	0.6
60°-70°	4.1	0.3
70°-80°	2.4	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1160.7	89.0
0°-40°	1265.4	97.1
0°-60°	1296.6	99.4
0°-90°	1303.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1303.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3047	
5°	2980	273
15°	2020	547
25°	724	340
35°	156	105
45°	27	23
55°	8	8
65°	3	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P224771

CATALOG NUMBER: LD2B15D010 EU2B15FL408035 2LBDL\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3047.3
2.5°	3033.9
5°	2980.4
7.5°	2844.9
10°	2619.1
12.5°	2348.2
15°	2020.4
17.5°	1662.4
20°	1307.9
22.5°	991.8
25°	724.2
27.5°	510.1
30°	349.5
32.5°	235.8
35°	155.5
37.5°	93.7
40°	58.5
42.5°	40.1
45°	26.8
47.5°	18.4
50°	13.4
52.5°	11.7
55°	8.4
57.5°	6.7
60°	6.7
62.5°	5.0
65°	3.3
67.5°	3.3
70°	3.3
72.5°	3.3
75°	1.7
77.5°	1.7
80°	1.7
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)