

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223328

Luminaire Tested: **LD2B15D010 EU2B15NFL258035 2LBDL\*B**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223328  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B15D010 EU2B15NFL258035 2LBDL\*B  
Description: 1500 Lumen, 2inch Portfolio LED Downlight  
NARROW FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH BLACK FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1381.0 lumens  
Efficiency: N/A  
Efficacy: 96.6 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223328

CATALOG NUMBER: LD2B15D010 EU2B15NFL258035 2LBDL\*B

### Luminous Intensity Polar Plot







TEST NUMBER: P223328

CATALOG NUMBER: LD2B15D010 EU2B15NFL258035 2LBDL\*B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	641.0	46.4
10°-20°	539.0	39.0
20°-30°	147.9	10.7
30°-40°	43.1	3.1
40°-50°	8.0	0.6
50°-60°	1.8	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1327.9	96.2
0°-40°	1371.0	99.3
0°-60°	1380.8	100.0
0°-90°	1381.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1381.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8193	
5°	7536	641
15°	1683	539
25°	307	148
35°	67	43
45°	10	8
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223328

CATALOG NUMBER: LD2B15D010 EU2B15NFL258035 2LBDL\*B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8193.0
1°	8145.3
2°	8061.0
3°	7939.9
4°	7774.0
5°	7535.9
6°	7210.8
7°	6804.1
8°	6307.6
9°	5721.3
10°	5042.5
11°	4298.5
12°	3524.5
13°	2785.8
14°	2156.0
15°	1682.7
17.5°	949.5
20°	601.2
22.5°	428.5
25°	307.4
27.5°	217.6
30°	151.0
32.5°	106.1
35°	66.7
37.5°	27.2
40°	20.4
42.5°	15.0
45°	9.5
47.5°	5.4
50°	4.1
52.5°	2.7
55°	1.4
57.5°	1.4
60°	1.4
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223328

CATALOG NUMBER: LD2B15D010 EU2B15NFL258035 2LBDL\*B

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)