

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B10D010 EU2B10WFL558035 2LBDSQLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10WFL558035 2LBDSQLC*MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 866.0 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL558035 2LBDSQLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL558035 2LBDSQLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93				93
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86				86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80				80
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74				74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69				69
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60				60
8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56
9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53				53
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49				49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	406171
5°	403601
10°	375189
15°	329390
20°	283927
25°	242800
30°	192683
35°	134340
40°	84999
45°	51876
50°	30673
55°	16815
60°	3641
65°	3300
70°	2718
75°	3592
80°	2677
85°	5333



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL558035 2LBDSQLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.3	11.1
10°-20°	228.8	26.4
20°-30°	258.1	29.8
30°-40°	178.6	20.6
40°-50°	76.1	8.8
50°-60°	22.0	2.5
60°-70°	3.2	0.4
70°-80°	2.1	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	583.2	67.3
0°-40°	761.7	88.0
0°-60°	859.9	99.3
0°-90°	866.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	866.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1049	
5°	1038	96
15°	821	229
25°	568	258
35°	284	179
45°	95	76
55°	25	22
65°	4	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL558035 2LBDSQLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1048.6
2.5°	1047.5
5°	1038.0
7.5°	1006.0
10°	953.9
12.5°	890.0
15°	821.4
17.5°	750.4
20°	688.8
22.5°	630.8
25°	568.1
27.5°	501.8
30°	430.8
32.5°	353.9
35°	284.1
37.5°	220.1
40°	168.1
42.5°	126.6
45°	94.7
47.5°	68.6
50°	50.9
52.5°	36.7
55°	24.9
57.5°	10.7
60°	4.7
62.5°	3.6
65°	3.6
67.5°	2.4
70°	2.4
72.5°	2.4
75°	2.4
77.5°	1.2
80°	1.2
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)