

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223244

Luminaire Tested: **LD2B15D010 EU2B15NFL258035 2LBDSQC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223244  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B15D010 EU2B15NFL258035 2LBDSQC\*MB  
Description: 1500 Lumen, 2inch Portfolio LED Downlight  
NARROW FLOOD OPTIC  
SQUARE CAST TRIM WITH MATTE BLACK FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1307.4 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223244

CATALOG NUMBER: LD2B15D010 EU2B15NFL258035 2LBDSQC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P223244

CATALOG NUMBER: LD2B15D010 EU2B15NFL258035 2LBDSQC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	95	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	92	92
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	90	90	90
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	88	88	88
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	86	86	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84	84	84	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	82	82	82
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	80	80	80
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79	79	79	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3004372
5°	2773998
10°	1877638
15°	638809
20°	234627
25°	124370
30°	63915
35°	29838
40°	9759
45°	4930
50°	2350
55°	878
60°	1007
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223244

CATALOG NUMBER: LD2B15D010 EU2B15NFL258035 2LBDSQC\*MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	606.9	46.4
10°-20°	510.3	39.0
20°-30°	140.0	10.7
30°-40°	40.8	3.1
40°-50°	7.6	0.6
50°-60°	1.7	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1257.1	96.2
0°-40°	1298.0	99.3
0°-60°	1307.3	100.0
0°-90°	1307.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1307.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7756	
5°	7134	607
15°	1593	510
25°	291	140
35°	63	41
45°	9	8
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223244

CATALOG NUMBER: LD2B15D010 EU2B15NFL258035 2LBDSQC\*MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7756.3
1°	7711.2
2°	7631.4
3°	7516.8
4°	7359.7
5°	7134.3
6°	6826.5
7°	6441.5
8°	5971.4
9°	5416.4
10°	4773.8
11°	4069.4
12°	3336.6
13°	2637.4
14°	2041.1
15°	1593.0
17.5°	898.9
20°	569.2
22.5°	405.7
25°	291.0
27.5°	206.0
30°	142.9
32.5°	100.4
35°	63.1
37.5°	25.8
40°	19.3
42.5°	14.2
45°	9.0
47.5°	5.2
50°	3.9
52.5°	2.6
55°	1.3
57.5°	1.3
60°	1.3
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223244

CATALOG NUMBER: LD2B15D010 EU2B15NFL258035 2LBDSQC\*MB

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)