

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265019

Luminaire Tested: **LD2B10D010 EU2B1010SP159035 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265019
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP159035 2LBDL*MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 807.0 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265019

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P265019

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97						97													
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94						94													
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92						92													
4	106	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89						89													
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87						87													
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85						85													
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83						83													
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81						81													
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79						79													
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	79	78						78													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2848868
5°	2318694
10°	1252482
15°	499427
20°	200244
25°	95917
30°	49734
35°	26260
40°	14555
45°	9001
50°	6217
55°	4129
60°	3158
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265019

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	376.5	46.7
10°-20°	297.1	36.8
20°-30°	87.6	10.9
30°-40°	29.2	3.6
40°-50°	11.0	1.4
50°-60°	4.8	0.6
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	761.2	94.3
0°-40°	790.4	97.9
0°-60°	806.2	99.9
0°-90°	807.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	807.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5774	
5°	4682	377
15°	978	297
25°	176	88
35°	44	29
45°	13	11
55°	5	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265019

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5774.4
2.5°	5541.7
5°	4681.9
7.5°	3607.2
10°	2500.1
12.5°	1600.0
15°	977.8
17.5°	596.3
20°	381.4
22.5°	255.3
25°	176.2
27.5°	124.4
30°	87.3
32.5°	61.4
35°	43.6
37.5°	30.7
40°	22.6
42.5°	17.8
45°	12.9
47.5°	11.3
50°	8.1
52.5°	6.5
55°	4.8
57.5°	4.8
60°	3.2
62.5°	1.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)