

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265022

Luminaire Tested: **LD2B10D010 EU2B1010SP159035 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265022
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP159035 2LBDL*WMH
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 764.0 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265022

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P265022

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97																																				
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94																																				
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92																																				
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89																																				
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87																																				
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85																																				
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83																																				
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81																																				
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79																																				
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2697061
5°	2195130
10°	1185752
15°	472816
20°	189586
25°	90800
30°	47056
35°	24874
40°	13782
45°	8512
50°	5910
55°	3957
60°	3059
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265022

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	356.5	46.7
10°-20°	281.2	36.8
20°-30°	83.0	10.9
30°-40°	27.6	3.6
40°-50°	10.4	1.4
50°-60°	4.6	0.6
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	720.7	94.3
0°-40°	748.3	97.9
0°-60°	763.3	99.9
0°-90°	764.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	764.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5467	
5°	4432	356
15°	926	281
25°	167	83
35°	41	28
45°	12	10
55°	5	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265022

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5466.7
2.5°	5246.4
5°	4432.4
7.5°	3415.0
10°	2366.9
12.5°	1514.7
15°	925.7
17.5°	564.6
20°	361.1
22.5°	241.7
25°	166.8
27.5°	117.8
30°	82.6
32.5°	58.1
35°	41.3
37.5°	29.1
40°	21.4
42.5°	16.8
45°	12.2
47.5°	10.7
50°	7.7
52.5°	6.1
55°	4.6
57.5°	4.6
60°	3.1
62.5°	1.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)