

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264353

Luminaire Tested: **LD2B10D010 EU2B1010SP159035 2LBSQC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264353  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B1010SP159035 2LBSQC\*MMS  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 841.0 lumens  
Efficiency: N/A  
Efficacy: 81.7 lumens/watt  
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264353

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBSQC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P264353

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBSQC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	98	98	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	96	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94	94	94	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92	92	92	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90	90	90	90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89	89	89	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87	87	87	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86	86	86	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85	85	85	85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83	83	83	83

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3968356
5°	3180819
10°	1388296
15°	430218
20°	150000
25°	66249
30°	29965
35°	15599
40°	8888
45°	4186
50°	2686
55°	1462
60°	888
65°	1051
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264353

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBSQC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	487.7	58.0
10°-20°	267.1	31.8
20°-30°	60.9	7.2
30°-40°	17.5	2.1
40°-50°	5.4	0.6
50°-60°	1.6	0.2
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	815.7	97.0
0°-40°	833.2	99.1
0°-60°	840.3	99.9
0°-90°	841.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	841.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8044	
5°	6423	488
15°	842	267
25°	122	61
35°	26	17
45°	6	5
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264353

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBSQC\*MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8043.5
1°	7943.4
2°	7735.4
3°	7412.6
4°	6969.0
5°	6422.7
6°	5753.0
7°	5004.7
8°	4223.7
9°	3467.7
10°	2771.2
11°	2181.8
12°	1717.4
13°	1351.5
14°	1067.6
15°	842.3
16°	664.5
17°	529.0
18°	425.5
19°	346.1
20°	285.7
22.5°	184.7
25°	121.7
26°	102.7
27°	87.2
28°	73.4
29°	61.3
30°	52.6
32.5°	36.2
35°	25.9
37.5°	19.0
40°	13.8
42.5°	9.5
45°	6.0
47.5°	4.3
50°	3.5
52.5°	2.6
55°	1.7
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.9



TEST NUMBER: P264353

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBSQC\*MMS

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)