

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224319

Luminaire Tested: **LD2B15D010 EU2B15FL409035 2LBDSQLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224319
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL409035 2LBDSQLC*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1020.0 lumens
Efficiency: N/A
Efficacy: 71.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224319

CATALOG NUMBER: LD2B15D010 EU2B15FL409035 2LBDSQLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224319

CATALOG NUMBER: LD2B15D010 EU2B15FL409035 2LBDSQLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95					95			
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91					91			
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86					86			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82					82			
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79					79			
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75					75			
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72					72			
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69					69			
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66					66			
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64					64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	923433
5°	906586
10°	805916
15°	633837
20°	421768
25°	242159
30°	122328
35°	57547
40°	23159
45°	11449
50°	6327
55°	4390
60°	4028
65°	2383
70°	2945
75°	1946
80°	2900
85°	0



TEST NUMBER: P224319

CATALOG NUMBER: LD2B15D010 EU2B15FL409035 2LBDSQLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.5	20.9
10°-20°	428.1	42.0
20°-30°	266.4	26.1
30°-40°	81.9	8.0
40°-50°	18.0	1.8
50°-60°	6.4	0.6
60°-70°	3.2	0.3
70°-80°	1.9	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	908.1	89.0
0°-40°	990.0	97.1
0°-60°	1014.4	99.4
0°-90°	1020.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1020.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2384	
5°	2332	214
15°	1581	428
25°	567	266
35°	122	82
45°	21	18
55°	6	6
65°	3	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P224319

CATALOG NUMBER: LD2B15D010 EU2B15FL409035 2LBDSQLC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2384.0
2.5°	2373.5
5°	2331.6
7.5°	2225.6
10°	2049.0
12.5°	1837.0
15°	1580.6
17.5°	1300.6
20°	1023.2
22.5°	775.9
25°	566.6
27.5°	399.1
30°	273.5
32.5°	184.5
35°	121.7
37.5°	73.3
40°	45.8
42.5°	31.4
45°	20.9
47.5°	14.4
50°	10.5
52.5°	9.2
55°	6.5
57.5°	5.2
60°	5.2
62.5°	3.9
65°	2.6
67.5°	2.6
70°	2.6
72.5°	2.6
75°	1.3
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)