

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223761

Luminaire Tested: **LD2B10D010 EU2B10SP159035 2LBDC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223761  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA ( 150)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10SP159035 2LBDC\*MB  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
SPOT OPTIC  
CAST ROUND TRIM WITH MATTE BLACK FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 492.3 lumens  
Efficiency: N/A  
Efficacy: 47.8 lumens/watt  
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223761

CATALOG NUMBER: LD2B10D010 EU2B10SP159035 2LBDC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P223761

CATALOG NUMBER: LD2B10D010 EU2B10SP159035 2LBDC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98									98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96									96																			
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94									94																			
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	91									91																			
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	89									89																			
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	88									88																			
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	86									86																			
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	85									85																			
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	84									84																			
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	83									83																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2365599
5°	1710094
10°	497866
15°	174680
20°	74774
25°	33636
30°	13016
35°	6478
40°	4349
45°	2794
50°	1567
55°	1148
60°	697
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223761

CATALOG NUMBER: LD2B10D010 EU2B10SP159035 2LBDC\*MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	311.2	63.2
10°-20°	126.6	25.7
20°-30°	38.9	7.9
30°-40°	9.6	1.9
40°-50°	4.0	0.8
50°-60°	1.7	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	476.7	96.8
0°-40°	486.3	98.8
0°-60°	492.0	99.9
0°-90°	492.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	492.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6107	
5°	4398	311
15°	436	127
25°	79	39
35°	14	10
45°	5	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223761

CATALOG NUMBER: LD2B10D010 EU2B10SP159035 2LBDC\*MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6107.2
1°	6013.9
2°	5786.3
3°	5423.4
4°	4949.3
5°	4398.1
6°	3776.8
7°	3102.4
8°	2418.6
9°	1779.3
10°	1265.8
11°	907.2
12°	682.1
13°	555.4
14°	486.1
15°	435.6
17.5°	268.7
20°	181.4
22.5°	121.5
25°	78.7
27.5°	47.9
30°	29.1
32.5°	18.8
35°	13.7
37.5°	11.1
40°	8.6
42.5°	6.8
45°	5.1
47.5°	3.4
50°	2.6
52.5°	2.6
55°	1.7
57.5°	1.7
60°	0.9
62.5°	0.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223761

CATALOG NUMBER: LD2B10D010 EU2B10SP159035 2LBDC\*MB

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)