

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B10D010 EU2B1010SP158040 2LBPIN**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14823)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP158040 2LBPIN
Description: 1000 Lumen, 2inch Portfolio LED Downlight
SPOT OPTIC
ROUND PINHOLE BLACK OCULUS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 508.3 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.24
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LD2B10D010 EU2B1010SP158040 2LBPIN

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B1010SP158040 2LBPIN

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98	98	98	98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96	96	96	96
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	95	95	95	95
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93	93	93	93
5	105	101	97	95	104	100	97	95	98	96	94	97	95	93	96	94	92	91	91	91	91
6	103	98	95	93	102	98	95	92	97	94	92	95	93	91	94	92	91	90	90	90	90
7	101	96	93	91	101	96	93	91	95	92	90	94	92	90	93	91	89	89	89	89	89
8	100	95	91	89	99	94	91	89	93	91	89	93	90	88	92	90	88	87	87	87	87
9	98	93	90	88	97	93	90	88	92	89	87	91	89	87	91	89	87	86	86	86	86
10	97	92	88	86	96	91	88	86	91	88	86	90	88	86	90	87	86	85	85	85	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2332042
5°	1728913
10°	537589
15°	171293
20°	74636
25°	33092
30°	12215
35°	5913
40°	4047
45°	2521
50°	1386
55°	1554
60°	852
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B1010SP158040 2LBPIN

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	321.5	63.3
10°-20°	134.3	26.4
20°-30°	38.4	7.6
30°-40°	8.6	1.7
40°-50°	3.6	0.7
50°-60°	1.6	0.3
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	494.3	97.2
0°-40°	502.9	98.9
0°-60°	508.1	100.0
0°-90°	508.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	508.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6018	
5°	4445	321
15°	427	134
25°	77	38
35°	12	9
45°	5	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B1010SP158040 2LBPIN

CANDELA DISTRIBUTION (FULL):

	0°
0°	6018.4
2.5°	5642.6
5°	4444.9
7.5°	2833.8
10°	1366.3
12.5°	635.3
15°	427.0
17.5°	265.3
20°	181.0
22.5°	123.0
25°	77.4
27.5°	45.5
30°	27.3
32.5°	17.1
35°	12.5
37.5°	9.1
40°	8.0
42.5°	5.7
45°	4.6
47.5°	3.4
50°	2.3
52.5°	2.3
55°	2.3
57.5°	1.1
60°	1.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)