

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264778

Luminaire Tested: **LD2B15D010 EU2B1510SP158040 2LBLC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264778  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B15D010 EU2B1510SP158040 2LBLC\*MW  
Description: 1500 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1432.0 lumens  
Efficiency: N/A  
Efficacy: 100.1 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264778

CATALOG NUMBER: LD2B15D010 EU2B1510SP158040 2LBLC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P264778

CATALOG NUMBER: LD2B15D010 EU2B1510SP158040 2LBLC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83	83	83	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79	79	79	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78	78	78	78

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	5055232
5°	4114457
10°	2222515
15°	886179
20°	355337
25°	170168
30°	88244
35°	46617
40°	25826
45°	15978
50°	10976
55°	7397
60°	5624
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264778

CATALOG NUMBER: LD2B15D010 EU2B1510SP158040 2LBLC\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	668.1	46.7
10°-20°	527.1	36.8
20°-30°	155.5	10.9
30°-40°	51.8	3.6
40°-50°	19.4	1.4
50°-60°	8.6	0.6
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1350.8	94.3
0°-40°	1402.5	97.9
0°-60°	1430.6	99.9
0°-90°	1432.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1432.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10246	
5°	8308	668
15°	1735	527
25°	313	156
35°	77	52
45°	23	19
55°	9	9
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264778

CATALOG NUMBER: LD2B15D010 EU2B1510SP158040 2LBLC\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10246.5
2.5°	9833.6
5°	8307.9
7.5°	6400.9
10°	4436.4
12.5°	2839.1
15°	1735.0
17.5°	1058.2
20°	676.8
22.5°	453.1
25°	312.6
27.5°	220.8
30°	154.9
32.5°	109.0
35°	77.4
37.5°	54.5
40°	40.1
42.5°	31.5
45°	22.9
47.5°	20.1
50°	14.3
52.5°	11.5
55°	8.6
57.5°	8.6
60°	5.7
62.5°	2.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)