

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224457

Luminaire Tested: **LD2B15D010 EU2B15FL408040 2LBDL\*WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224457  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B15D010 EU2B15FL408040 2LBDL\*WH  
Description: 1500 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1393.2 lumens  
Efficiency: N/A  
Efficacy: 97.4 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224457

CATALOG NUMBER: LD2B15D010 EU2B15FL408040 2LBDL\*WH

### Luminous Intensity Polar Plot





TEST NUMBER: P224457

CATALOG NUMBER: LD2B15D010 EU2B15FL408040 2LBDL\*WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87			87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79			79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75			75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72			72
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66			66
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1285446
5°	1236815
10°	1088674
15°	855114
20°	581374
25°	339518
30°	172914
35°	81805
40°	35698
45°	15448
50°	7472
55°	4795
60°	2711
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224457

CATALOG NUMBER: LD2B15D010 EU2B15FL408040 2LBDL\*WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	290.5	20.9
10°-20°	579.9	41.6
20°-30°	372.2	26.7
30°-40°	118.1	8.5
40°-50°	25.2	1.8
50°-60°	6.5	0.5
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1242.6	89.2
0°-40°	1360.7	97.7
0°-60°	1392.3	99.9
0°-90°	1393.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1393.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3319	
5°	3181	291
15°	2132	580
25°	794	372
35°	173	118
45°	28	25
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224457

CATALOG NUMBER: LD2B15D010 EU2B15FL408040 2LBDL\*WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3318.6
2.5°	3286.9
5°	3180.9
7.5°	3008.0
10°	2767.9
12.5°	2474.9
15°	2132.4
17.5°	1767.0
20°	1410.4
22.5°	1076.8
25°	794.4
27.5°	566.6
30°	386.6
32.5°	259.5
35°	173.0
37.5°	114.7
40°	70.6
42.5°	44.1
45°	28.2
47.5°	19.4
50°	12.4
52.5°	8.8
55°	7.1
57.5°	5.3
60°	3.5
62.5°	1.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)