

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224274

Luminaire Tested: **LD2B10D010 EU2B10FL408040 2LBDSQLC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224274  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10FL408040 2LBDSQLC\*MMS  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
LENSED SQUARE CAST TRIM WITH MATTE METALLIC SILVER  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 951.3 lumens  
Efficiency: N/A  
Efficacy: 92.4 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224274

CATALOG NUMBER: LD2B10D010 EU2B10FL408040 2LBDSQLC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P224274

CATALOG NUMBER: LD2B10D010 EU2B10FL408040 2LBDSQLC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	87	87	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83	83	83	83
5	98	91	86	83	96	90	86	82	88	85	82	87	83	81	85	83	80	79	79	79	79
6	94	87	82	78	93	86	82	78	85	81	78	83	80	77	82	79	77	76	76	76	76
7	91	83	78	75	89	82	78	75	81	77	74	80	77	74	79	76	73	72	72	72	72
8	87	80	75	71	86	79	75	71	78	74	71	77	73	71	76	73	70	69	69	69	69
9	84	76	72	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	67	67
10	81	74	69	66	81	73	69	66	72	68	65	72	68	65	71	68	65	64	64	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	865951
5°	849312
10°	754430
15°	595380
20°	397077
25°	228568
30°	115753
35°	54285
40°	22248
45°	10025
50°	5122
55°	3309
60°	1859
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224274

CATALOG NUMBER: LD2B10D010 EU2B10FL408040 2LBDSQLC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	199.9	21.0
10°-20°	401.2	42.2
20°-30°	251.3	26.4
30°-40°	77.8	8.2
40°-50°	16.1	1.7
50°-60°	4.5	0.5
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	852.4	89.6
0°-40°	930.2	97.8
0°-60°	950.7	99.9
0°-90°	951.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	951.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2236	
5°	2184	200
15°	1485	401
25°	535	251
35°	115	78
45°	18	16
55°	5	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224274

CATALOG NUMBER: LD2B10D010 EU2B10FL408040 2LBDSQLC\*MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2235.6
2.5°	2224.6
5°	2184.3
7.5°	2081.7
10°	1918.1
12.5°	1716.7
15°	1484.7
17.5°	1217.3
20°	963.3
22.5°	732.6
25°	534.8
27.5°	376.1
30°	258.8
32.5°	173.4
35°	114.8
37.5°	72.0
40°	44.0
42.5°	28.1
45°	18.3
47.5°	12.2
50°	8.5
52.5°	6.1
55°	4.9
57.5°	3.7
60°	2.4
62.5°	1.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)