

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223146

Luminaire Tested: **LD2B15D010 EU2B15NFL258040 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223146
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15NFL258040 2LBDC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1433.1 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223146

CATALOG NUMBER: LD2B15D010 EU2B15NFL258040 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P223146

CATALOG NUMBER: LD2B15D010 EU2B15NFL258040 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	95	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	92	92
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	90	90	90
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	88	88	88
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	86	86	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	87	85	84	84	84	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	82	82	82
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	80	80	80
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79	79	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3293216
5°	3040694
10°	2058172
15°	700204
20°	257175
25°	136337
30°	70087
35°	32722
40°	10720
45°	5423
50°	2531
55°	945
60°	1085
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223146

CATALOG NUMBER: LD2B15D010 EU2B15NFL258040 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	665.2	46.4
10°-20°	559.3	39.0
20°-30°	153.5	10.7
30°-40°	44.8	3.1
40°-50°	8.3	0.6
50°-60°	1.9	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1378.0	96.2
0°-40°	1422.8	99.3
0°-60°	1432.9	100.0
0°-90°	1433.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1433.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8502	
5°	7820	665
15°	1746	559
25°	319	154
35°	69	45
45°	10	8
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223146

CATALOG NUMBER: LD2B15D010 EU2B15NFL258040 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	8502.0
1°	8452.6
2°	8365.1
3°	8239.5
4°	8067.3
5°	7820.2
6°	7482.9
7°	7060.8
8°	6545.6
9°	5937.2
10°	5232.8
11°	4460.6
12°	3657.4
13°	2890.9
14°	2237.4
15°	1746.1
17.5°	985.3
20°	623.9
22.5°	444.7
25°	319.0
27.5°	225.9
30°	156.7
32.5°	110.1
35°	69.2
37.5°	28.2
40°	21.2
42.5°	15.5
45°	9.9
47.5°	5.6
50°	4.2
52.5°	2.8
55°	1.4
57.5°	1.4
60°	1.4
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223146

CATALOG NUMBER: LD2B15D010 EU2B15NFL258040 2LBDC*MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)